

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793169

Luminaire Tested: LER6D45BD010-EC6DR7040509030-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P793169
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D45BD010-EC6DR7040509030-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5197.3 lumens
Efficiency: N/A
Efficacy: 134.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P793169

CATALOG NUMBER: LER6D45BD010-EC6DR7040509030-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P793169

CATALOG NUMBER: LER6D45BD010-EC6DR7040509030-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	638454
5°	619473
10°	602216
15°	594307
20°	554959
25°	416918
30°	294718
35°	104399
40°	54898
45°	58470
50°	60547
55°	61681
60°	62060
65°	60755
70°	57343
75°	53107
80°	47128
85°	38236

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 62083 cd/sqm



TEST NUMBER: P793169

CATALOG NUMBER: LER6D45BD010-EC6DR7040509030-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	532.7	10.3
10°-20°	1461.3	28.1
20°-30°	1609.4	31.0
30°-40°	614.9	11.8
40°-50°	290.4	5.6
50°-60°	288.7	5.6
60°-70°	231.1	4.4
70°-80°	132.8	2.6
80°-90°	36.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3603.4	69.3
0°-40°	4218.3	81.2
0°-60°	4797.4	92.3
0°-90°	5197.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5197.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5843	
5°	5648	533
15°	5254	1461
25°	3458	1609
35°	783	615
45°	378	290
55°	324	289
65°	235	231
75°	126	133
85°	30	36
90°	0	



TEST NUMBER: P793169

CATALOG NUMBER: LER6D45BD010-EC6DR7040509030-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	5843.4
2.5°	5782.3
5°	5648.1
7.5°	5536.2
10°	5428.0
12.5°	5336.4
15°	5254.0
17.5°	5055.1
20°	4772.9
22.5°	4164.2
25°	3458.3
27.5°	3010.5
30°	2336.0
32.5°	1508.9
35°	782.7
37.5°	422.8
40°	384.9
42.5°	382.1
45°	378.4
47.5°	370.1
50°	356.2
52.5°	340.5
55°	323.8
57.5°	305.3
60°	284.0
62.5°	260.0
65°	235.0
67.5°	207.2
70°	179.5
72.5°	151.7
75°	125.8
77.5°	99.0
80°	74.9
82.5°	52.7
85°	30.5
87.5°	12.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)