

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793176

Luminaire Tested: LER6D45BD010-EC6DR7040509035-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P793176
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D45BD010-EC6DR7040509035-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5002.0 lumens
Efficiency: N/A
Efficacy: 129.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P793176

CATALOG NUMBER: LER6D45BD010-EC6DR7040509035-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P793176

CATALOG NUMBER: LER6D45BD010-EC6DR7040509035-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	614450
5°	596188
10°	579572
15°	571966
20°	534099
25°	401246
30°	283641
35°	100477
40°	52830
45°	56275
50°	58269
55°	59357
60°	59744
65°	58480
70°	55170
75°	51123
80°	45366
85°	36857

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 59745 cd/sqm



TEST NUMBER: P793176

CATALOG NUMBER: LER6D45BD010-EC6DR7040509035-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	512.7	10.3
10°-20°	1406.4	28.1
20°-30°	1548.9	31.0
30°-40°	591.8	11.8
40°-50°	279.4	5.6
50°-60°	277.8	5.6
60°-70°	222.4	4.4
70°-80°	127.8	2.6
80°-90°	34.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3468.0	69.3
0°-40°	4059.8	81.2
0°-60°	4617.0	92.3
0°-90°	5002.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5002.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5624	
5°	5436	513
15°	5056	1406
25°	3328	1549
35°	753	592
45°	364	279
55°	312	278
65°	226	222
75°	121	128
85°	29	35
90°	0	



TEST NUMBER: P793176

CATALOG NUMBER: LER6D45BD010-EC6DR7040509035-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	5623.7
2.5°	5565.0
5°	5435.8
7.5°	5328.1
10°	5223.9
12.5°	5135.8
15°	5056.5
17.5°	4865.1
20°	4593.5
22.5°	4007.7
25°	3328.3
27.5°	2897.3
30°	2248.2
32.5°	1452.2
35°	753.3
37.5°	406.9
40°	370.4
42.5°	367.7
45°	364.2
47.5°	356.2
50°	342.8
52.5°	327.7
55°	311.6
57.5°	293.8
60°	273.4
62.5°	250.2
65°	226.2
67.5°	199.4
70°	172.7
72.5°	146.0
75°	121.1
77.5°	95.3
80°	72.1
82.5°	50.8
85°	29.4
87.5°	11.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)