

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792182

Luminaire Tested: LER6D35BD010-EC6DR6520359040-6LBS1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P792182  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D35BD010-EC6DR6520359040-6LBS1MW  
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3525.6 lumens  
Efficiency: N/A  
Efficacy: 114.5 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 30.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P792182  
CATALOG NUMBER: LER6D35BD010-EC6DR6520359040-6LBS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P792182

CATALOG NUMBER: LER6D35BD010-EC6DR6520359040-6LBS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |     |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF  | 20  |     |     |     |     |     |     |     |     | 20  |     |     |     |     |     |     |     |     | 20 |    |     |  |  |  |  |  |  | 20 |  |  |  |  |  |  |  |  |   |
| RC  | 80  |     |     |     |     |     |     |     |     | 50  |     |     |     |     |     |     |     |     | 30 |    |     |  |  |  |  |  |  | 10 |  |  |  |  |  |  |  |  | 0 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |     |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    | 100 |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 1   | 113 | 110 | 107 | 105 | 111 | 108 | 105 | 103 | 104 | 102 | 100 | 100 | 99  | 97  | 97  | 95  | 94  | 93  |    |    | 93  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 2   | 107 | 102 | 97  | 94  | 105 | 100 | 96  | 92  | 97  | 93  | 90  | 94  | 91  | 88  | 91  | 89  | 87  | 85  |    |    | 85  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 3   | 101 | 94  | 88  | 84  | 99  | 92  | 87  | 83  | 90  | 86  | 82  | 87  | 84  | 81  | 85  | 82  | 80  | 78  |    |    | 78  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 4   | 95  | 87  | 81  | 76  | 93  | 86  | 80  | 76  | 84  | 79  | 75  | 82  | 77  | 74  | 80  | 76  | 73  | 72  |    |    | 72  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 5   | 90  | 81  | 74  | 70  | 88  | 80  | 74  | 69  | 78  | 73  | 69  | 76  | 72  | 68  | 75  | 71  | 68  | 66  |    |    | 66  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 6   | 85  | 75  | 69  | 64  | 83  | 74  | 68  | 64  | 73  | 67  | 63  | 71  | 67  | 63  | 70  | 66  | 62  | 61  |    |    | 61  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 7   | 80  | 70  | 64  | 59  | 79  | 69  | 63  | 59  | 68  | 63  | 59  | 67  | 62  | 58  | 66  | 61  | 58  | 56  |    |    | 56  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 8   | 76  | 66  | 59  | 55  | 75  | 65  | 59  | 55  | 64  | 58  | 54  | 63  | 58  | 54  | 62  | 57  | 54  | 52  |    |    | 52  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 9   | 72  | 61  | 55  | 51  | 71  | 61  | 55  | 51  | 60  | 54  | 51  | 59  | 54  | 50  | 58  | 54  | 50  | 49  |    |    | 49  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 10  | 68  | 58  | 52  | 47  | 67  | 57  | 51  | 47  | 57  | 51  | 47  | 56  | 51  | 47  | 55  | 50  | 47  | 46  |    |    | 46  |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 186957 |
| 5°  | 186487 |
| 10° | 186324 |
| 15° | 180582 |
| 20° | 164399 |
| 25° | 143260 |
| 30° | 119151 |
| 35° | 94413  |
| 40° | 68144  |
| 45° | 43049  |
| 50° | 22442  |
| 55° | 11924  |
| 60° | 6261   |
| 65° | 3441   |
| 70° | 1451   |
| 75° | 1602   |
| 80° | 1110   |
| 85° | 938    |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 43049 cd/sqm



TEST NUMBER: P792182

CATALOG NUMBER: LER6D35BD010-EC6DR6520359040-6LBS1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 302.7  | 8.6       |
| 10°-20°   | 829.0  | 23.5      |
| 20°-30°   | 1013.3 | 28.7      |
| 30°-40°   | 822.2  | 23.3      |
| 40°-50°   | 409.7  | 11.6      |
| 50°-60°   | 114.3  | 3.2       |
| 60°-70°   | 26.0   | 0.7       |
| 70°-80°   | 6.8    | 0.2       |
| 80°-90°   | 1.7    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 2145.0 | 60.8      |
| 0°-40°    | 2967.1 | 84.2      |
| 0°-60°    | 3491.1 | 99.0      |
| 0°-90°    | 3525.6 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 3525.6 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3201 |      |
| 5°  | 3181 | 303  |
| 15° | 2987 | 829  |
| 25° | 2223 | 1013 |
| 35° | 1324 | 822  |
| 45° | 521  | 410  |
| 55° | 117  | 114  |
| 65° | 25   | 26   |
| 75° | 7    | 7    |
| 85° | 1    | 2    |
| 90° | 0    |      |



TEST NUMBER: P792182

CATALOG NUMBER: LER6D35BD010-EC6DR6520359040-6LBS1MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 3201.1 |
| 2.5°  | 3198.8 |
| 5°    | 3180.9 |
| 7.5°  | 3170.5 |
| 10°   | 3141.8 |
| 12.5° | 3083.5 |
| 15°   | 2986.6 |
| 17.5° | 2835.1 |
| 20°   | 2645.1 |
| 22.5° | 2440.0 |
| 25°   | 2223.1 |
| 27.5° | 1991.2 |
| 30°   | 1766.8 |
| 32.5° | 1545.3 |
| 35°   | 1324.2 |
| 37.5° | 1103.6 |
| 40°   | 893.8  |
| 42.5° | 697.1  |
| 45°   | 521.2  |
| 47.5° | 363.2  |
| 50°   | 247.0  |
| 52.5° | 170.3  |
| 55°   | 117.1  |
| 57.5° | 79.0   |
| 60°   | 53.6   |
| 62.5° | 37.2   |
| 65°   | 24.9   |
| 67.5° | 12.7   |
| 70°   | 8.5    |
| 72.5° | 8.0    |
| 75°   | 7.1    |
| 77.5° | 4.7    |
| 80°   | 3.3    |
| 82.5° | 2.4    |
| 85°   | 1.4    |
| 87.5° | 0.9    |
| 90°   | 0.0    |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)