

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793185

Luminaire Tested: LER6D45BD010-EC6DR7040509040-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P793185
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D45BD010-EC6DR7040509040-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5497.7 lumens
Efficiency: N/A
Efficacy: 142.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P793185

CATALOG NUMBER: LER6D45BD010-EC6DR7040509040-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P793185

CATALOG NUMBER: LER6D45BD010-EC6DR7040509040-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	675341
5°	655272
10°	637009
15°	628648
20°	587027
25°	441006
30°	311750
35°	110428
40°	58065
45°	61854
50°	64048
55°	65243
60°	65644
65°	64271
70°	60665
75°	56188
80°	49896
85°	40492

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 65662 cd/sqm



TEST NUMBER: P793185

CATALOG NUMBER: LER6D45BD010-EC6DR7040509040-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	563.5	10.3
10°-20°	1545.7	28.1
20°-30°	1702.4	31.0
30°-40°	650.4	11.8
40°-50°	307.1	5.6
50°-60°	305.3	5.6
60°-70°	244.5	4.4
70°-80°	140.5	2.6
80°-90°	38.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3811.6	69.3
0°-40°	4462.1	81.2
0°-60°	5074.5	92.3
0°-90°	5497.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5497.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6181	
5°	5974	564
15°	5558	1546
25°	3658	1702
35°	828	650
45°	400	307
55°	342	305
65°	249	244
75°	133	141
85°	32	38
90°	0	



TEST NUMBER: P793185

CATALOG NUMBER: LER6D45BD010-EC6DR7040509040-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	6181.0
2.5°	6116.4
5°	5974.5
7.5°	5856.1
10°	5741.6
12.5°	5644.7
15°	5557.6
17.5°	5347.2
20°	5048.7
22.5°	4404.8
25°	3658.1
27.5°	3184.4
30°	2471.0
32.5°	1596.1
35°	827.9
37.5°	447.2
40°	407.1
42.5°	404.2
45°	400.3
47.5°	391.4
50°	376.8
52.5°	360.1
55°	342.5
57.5°	322.9
60°	300.4
62.5°	275.0
65°	248.6
67.5°	219.2
70°	189.9
72.5°	160.5
75°	133.1
77.5°	104.7
80°	79.3
82.5°	55.8
85°	32.3
87.5°	12.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)