

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792187

Luminaire Tested: LER6D35BD010-EC6DR6520359050-6LBS1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P792187  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D35BD010-EC6DR6520359050-6LBS1B  
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3469.4 lumens  
Efficiency: N/A  
Efficacy: 112.6 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct


Input Watts (W): 30.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P792187  
CATALOG NUMBER: LER6D35BD010-EC6DR6520359050-6LBS1B

### Luminous Intensity Polar Plot





TEST NUMBER: P792187  
 CATALOG NUMBER: LER6D35BD010-EC6DR6520359050-6LBS1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	183984
5°	183514
10°	183359
15°	177710
20°	161782
25°	140979
30°	117256
35°	92908
40°	67054
45°	42363
50°	22079
55°	11740
60°	6167
65°	3386
70°	1417
75°	1557
80°	1076
85°	938

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 42363 cd/sqm



TEST NUMBER: P792187

CATALOG NUMBER: LER6D35BD010-EC6DR6520359050-6LBS1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	297.9	8.6
10°-20°	815.8	23.5
20°-30°	997.2	28.7
30°-40°	809.1	23.3
40°-50°	403.2	11.6
50°-60°	112.5	3.2
60°-70°	25.6	0.7
70°-80°	6.6	0.2
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2110.8	60.8
0°-40°	2919.9	84.2
0°-60°	3435.5	99.0
0°-90°	3469.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3469.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3150	
5°	3130	298
15°	2939	816
25°	2188	997
35°	1303	809
45°	513	403
55°	115	112
65°	24	26
75°	7	7
85°	1	2
90°	0	



TEST NUMBER: P792187

CATALOG NUMBER: LER6D35BD010-EC6DR6520359050-6LBS1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3150.2
2.5°	3147.8
5°	3130.2
7.5°	3120.1
10°	3091.8
12.5°	3034.4
15°	2939.1
17.5°	2790.0
20°	2603.0
22.5°	2401.2
25°	2187.7
27.5°	1959.5
30°	1738.7
32.5°	1520.7
35°	1303.1
37.5°	1086.0
40°	879.5
42.5°	686.0
45°	512.9
47.5°	357.4
50°	243.0
52.5°	167.6
55°	115.3
57.5°	77.8
60°	52.8
62.5°	36.6
65°	24.5
67.5°	12.5
70°	8.3
72.5°	7.9
75°	6.9
77.5°	4.6
80°	3.2
82.5°	2.3
85°	1.4
87.5°	0.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)