

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793256

Luminaire Tested: LER6D50D010-EC6DR3040509027-6LBDP1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P793256  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D50D010-EC6DR3040509027-6LBDP1H  
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 30° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5458.9 lumens  
Efficiency: N/A  
Efficacy: 116.1 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49  
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')  
CIE Type: Direct


Input Watts (W): 47  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P793256  
CATALOG NUMBER: LER6D50D010-EC6DR3040509027-6LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P793256

CATALOG NUMBER: LER6D50D010-EC6DR3040509027-6LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1343559	1343559	1343559
5°	1304987	1303465	1305056
10°	1130320	1122345	1130048
15°	737472	733518	729825
20°	366714	380472	366217
25°	184723	208303	180939
30°	73960	80589	64441
35°	34303	32854	27537
40°	14808	16447	13949
45°	10446	12968	10543
50°	3596	9443	3799
55°	2068	3910	2189
60°	1454	1715	1454
65°	942	942	942
70°	582	380	582
75°	0	266	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 12968 cd/sqm



TEST NUMBER: P793256

CATALOG NUMBER: LER6D50D010-EC6DR3040509027-6LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1543.5	28.3
10°-20°	2485.8	45.5
20°-30°	1074.2	19.7
30°-40°	244.8	4.5
40°-50°	84.1	1.5
50°-60°	20.5	0.4
60°-70°	5.3	0.1
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5103.5	93.5
0°-40°	5348.4	98.0
0°-60°	5453.0	99.9
0°-90°	5458.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5458.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	17553	17553	17553	17553	17553	
5°	16984	16968	16964	17000	16985	1545
15°	9306	9194	9256	9226	9210	2492
25°	2187	2270	2466	2212	2142	1047
35°	367	375	352	349	295	249
45°	96	120	120	120	97	68
55°	16	16	29	17	16	15
65°	5	5	5	5	5	5
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P793256

CATALOG NUMBER: LER6D50D010-EC6DR3040509027-6LBDP1H

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	17552.9	17552.9	17552.9	17552.9	17552.9
2.5°	17436.5	17424.5	17431.4	17440.0	17443.4
5°	16984.1	16967.7	16964.3	16999.6	16985.0
7.5°	16071.5	16048.2	16012.9	16093.0	16168.0
10°	14542.7	14516.8	14440.1	14478.0	14539.2
12.5°	12285.6	12202.1	12200.3	12321.0	12304.6
15°	9306.4	9194.4	9256.5	9226.3	9209.9
17.5°	6258.3	6215.2	6297.9	6273.0	6165.2
20°	4502.0	4513.2	4670.9	4591.6	4495.9
22.5°	3285.1	3325.6	3512.6	3308.4	3233.4
25°	2187.2	2269.9	2466.4	2212.2	2142.4
27.5°	1345.3	1383.2	1582.2	1328.0	1290.1
30°	836.8	817.8	911.8	782.5	729.1
32.5°	549.0	524.8	555.0	498.1	455.0
35°	367.1	374.9	351.6	349.0	294.7
37.5°	229.2	263.7	232.7	248.2	189.6
40°	148.2	191.3	164.6	181.8	139.6
42.5°	121.5	147.4	135.3	143.9	124.1
45°	96.5	119.8	119.8	119.8	97.4
47.5°	53.4	80.1	102.6	81.9	56.9
50°	30.2	40.5	79.3	42.2	31.9
52.5°	20.7	23.3	54.3	24.1	21.5
55°	15.5	16.4	29.3	17.2	16.4
57.5°	12.1	12.9	15.5	12.9	12.1
60°	9.5	9.5	11.2	10.3	9.5
62.5°	6.9	6.9	7.8	6.9	6.9
65°	5.2	5.2	5.2	5.2	5.2
67.5°	2.6	3.4	3.4	3.4	3.4
70°	2.6	1.7	1.7	1.7	2.6
72.5°	1.7	0.9	0.9	0.9	0.9
75°	0.0	0.0	0.9	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)