

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792231

Luminaire Tested: LER6D35BD010-EC6DR7020359050-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P792231
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D35BD010-EC6DR7020359050-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2379.3 lumens
Efficiency: N/A
Efficacy: 77.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P792231

CATALOG NUMBER: LER6D35BD010-EC6DR7020359050-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P792231

CATALOG NUMBER: LER6D35BD010-EC6DR7020359050-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	292273
5°	283595
10°	275690
15°	272064
20°	254056
25°	190864
30°	134919
35°	47791
40°	25131
45°	26763
50°	27724
55°	28231
60°	28408
65°	27818
70°	26259
75°	24316
80°	21582
85°	17551

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 28429 cd/sqm



TEST NUMBER: P792231

CATALOG NUMBER: LER6D35BD010-EC6DR7020359050-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.9	10.3
10°-20°	669.0	28.1
20°-30°	736.8	31.0
30°-40°	281.5	11.8
40°-50°	132.9	5.6
50°-60°	132.2	5.6
60°-70°	105.8	4.4
70°-80°	60.8	2.6
80°-90°	16.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1649.6	69.3
0°-40°	1931.1	81.2
0°-60°	2196.2	92.3
0°-90°	2379.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2379.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2675	
5°	2586	244
15°	2405	669
25°	1583	737
35°	358	282
45°	173	133
55°	148	132
65°	108	106
75°	58	61
85°	14	17
90°	0	



TEST NUMBER: P792231

CATALOG NUMBER: LER6D35BD010-EC6DR7020359050-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2675.0
2.5°	2647.1
5°	2585.7
7.5°	2534.4
10°	2484.9
12.5°	2442.9
15°	2405.2
17.5°	2314.2
20°	2185.0
22.5°	1906.3
25°	1583.2
27.5°	1378.2
30°	1069.4
32.5°	690.8
35°	358.3
37.5°	193.6
40°	176.2
42.5°	174.9
45°	173.2
47.5°	169.4
50°	163.1
52.5°	155.9
55°	148.2
57.5°	139.8
60°	130.0
62.5°	119.0
65°	107.6
67.5°	94.9
70°	82.2
72.5°	69.5
75°	57.6
77.5°	45.3
80°	34.3
82.5°	24.1
85°	14.0
87.5°	5.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)