

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793584

Luminaire Tested: LER6D50D010-EC6DR6540509024-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P793584
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D50D010-EC6DR6540509024-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4324.1 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P793584
CATALOG NUMBER: LER6D50D010-EC6DR6540509024-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P793584

CATALOG NUMBER: LER6D50D010-EC6DR6540509024-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	465167
5°	465551
10°	481940
15°	482741
20°	444441
25°	378690
30°	289898
35°	204809
40°	120893
45°	49075
50°	17797
55°	9905
60°	5682
65°	3128
70°	3290
75°	2575
80°	2643
85°	2257

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 49075 cd/sqm



TEST NUMBER: P793584

CATALOG NUMBER: LER6D50D010-EC6DR6540509024-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	409.9	9.5
10°-20°	1182.5	27.3
20°-30°	1418.8	32.8
30°-40°	953.5	22.1
40°-50°	285.4	6.6
50°-60°	50.4	1.2
60°-70°	14.3	0.3
70°-80°	7.0	0.2
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3011.3	69.6
0°-40°	3964.8	91.7
0°-60°	4300.6	99.5
0°-90°	4324.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4324.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4257	
5°	4245	410
15°	4268	1183
25°	3141	1419
35°	1536	953
45°	318	285
55°	52	50
65°	12	14
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P793584

CATALOG NUMBER: LER6D50D010-EC6DR6540509024-6LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	4257.4
2.5°	4275.5
5°	4244.7
7.5°	4308.8
10°	4343.9
12.5°	4335.4
15°	4267.7
17.5°	4101.9
20°	3822.4
22.5°	3493.3
25°	3141.2
27.5°	2743.7
30°	2297.8
32.5°	1893.7
35°	1535.5
37.5°	1181.6
40°	847.6
42.5°	553.6
45°	317.6
47.5°	168.2
50°	104.7
52.5°	72.6
55°	52.0
57.5°	37.5
60°	26.0
62.5°	16.9
65°	12.1
67.5°	10.9
70°	10.3
72.5°	7.9
75°	6.1
77.5°	5.4
80°	4.2
82.5°	3.0
85°	1.8
87.5°	1.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)