

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793607

Luminaire Tested: LER6D50D010-EC6DR6540509035-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P793607
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D50D010-EC6DR6540509035-6LB DP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3798.6 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P793607
CATALOG NUMBER: LER6D50D010-EC6DR6540509035-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P793607

CATALOG NUMBER: LER6D50D010-EC6DR6540509035-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	408624
5°	408968
10°	423360
15°	424068
20°	390421
25°	332662
30°	254661
35°	179920
40°	106202
45°	43111
50°	15621
55°	8705
60°	5004
65°	2740
70°	2875
75°	2237
80°	2328
85°	2006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 43111 cd/sqm



TEST NUMBER: P793607

CATALOG NUMBER: LER6D50D010-EC6DR6540509035-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	360.1	9.5
10°-20°	1038.8	27.3
20°-30°	1246.4	32.8
30°-40°	837.6	22.1
40°-50°	250.7	6.6
50°-60°	44.3	1.2
60°-70°	12.6	0.3
70°-80°	6.2	0.2
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2645.3	69.6
0°-40°	3482.9	91.7
0°-60°	3777.9	99.5
0°-90°	3798.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3798.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3740	
5°	3729	360
15°	3749	1039
25°	2759	1246
35°	1349	838
45°	279	251
55°	46	44
65°	11	13
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P793607

CATALOG NUMBER: LER6D50D010-EC6DR6540509035-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3739.9
2.5°	3755.9
5°	3728.8
7.5°	3785.1
10°	3815.9
12.5°	3808.5
15°	3749.0
17.5°	3603.3
20°	3357.8
22.5°	3068.7
25°	2759.4
27.5°	2410.2
30°	2018.5
32.5°	1663.5
35°	1348.9
37.5°	1038.0
40°	744.6
42.5°	486.3
45°	279.0
47.5°	147.7
50°	91.9
52.5°	63.8
55°	45.7
57.5°	33.0
60°	22.9
62.5°	14.9
65°	10.6
67.5°	9.6
70°	9.0
72.5°	6.9
75°	5.3
77.5°	4.8
80°	3.7
82.5°	2.7
85°	1.6
87.5°	1.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)