

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793663

Luminaire Tested: LER6D50D010-EC6DR7040509040-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P793663
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D50D010-EC6DR7040509040-6LBDDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3577.6 lumens
Efficiency: N/A
Efficacy: 76.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P793663
CATALOG NUMBER: LER6D50D010-EC6DR7040509040-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P793663

CATALOG NUMBER: LER6D50D010-EC6DR7040509040-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	439480
5°	426418
10°	414540
15°	409092
20°	382015
25°	286983
30°	202871
35°	71867
40°	37783
45°	40252
50°	41679
55°	42460
60°	42721
65°	41831
70°	39453
75°	36558
80°	32467
85°	26326

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 42745 cd/sqm



TEST NUMBER: P793663

CATALOG NUMBER: LER6D50D010-EC6DR7040509040-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	366.7	10.3
10°-20°	1005.9	28.1
20°-30°	1107.8	31.0
30°-40°	423.3	11.8
40°-50°	199.9	5.6
50°-60°	198.7	5.6
60°-70°	159.1	4.4
70°-80°	91.4	2.6
80°-90°	24.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2480.4	69.3
0°-40°	2903.7	81.2
0°-60°	3302.3	92.3
0°-90°	3577.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3577.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4022	
5°	3888	367
15°	3617	1006
25°	2380	1108
35°	539	423
45°	260	200
55°	223	199
65°	162	159
75°	87	91
85°	21	25
90°	0	



TEST NUMBER: P793663

CATALOG NUMBER: LER6D50D010-EC6DR7040509040-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	4022.3
2.5°	3980.3
5°	3887.9
7.5°	3810.9
10°	3736.4
12.5°	3673.3
15°	3616.6
17.5°	3479.7
20°	3285.5
22.5°	2866.4
25°	2380.5
27.5°	2072.3
30°	1608.0
32.5°	1038.7
35°	538.8
37.5°	291.0
40°	264.9
42.5°	263.0
45°	260.5
47.5°	254.7
50°	245.2
52.5°	234.4
55°	222.9
57.5°	210.2
60°	195.5
62.5°	179.0
65°	161.8
67.5°	142.7
70°	123.5
72.5°	104.4
75°	86.6
77.5°	68.1
80°	51.6
82.5°	36.3
85°	21.0
87.5°	8.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)