

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793666

Luminaire Tested: LER6D50D010-EC6DR7040509040-6LBDP1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P793666  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D50D010-EC6DR7040509040-6LBDP1MW  
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4803.0 lumens  
Efficiency: N/A  
Efficacy: 102.2 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 47  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P793666

CATALOG NUMBER: LER6D50D010-EC6DR7040509040-6LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P793666

CATALOG NUMBER: LER6D50D010-EC6DR7040509040-6LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	589997
5°	572465
10°	556518
15°	549208
20°	512856
25°	385273
30°	272362
35°	96476
40°	50733
45°	54035
50°	55957
55°	56995
60°	57362
65°	56153
70°	52998
75°	49096
80°	43604
85°	35352

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 57365 cd/sqm



TEST NUMBER: P793666

CATALOG NUMBER: LER6D50D010-EC6DR7040509040-6LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	492.3	10.3
10°-20°	1350.4	28.1
20°-30°	1487.3	31.0
30°-40°	568.2	11.8
40°-50°	268.3	5.6
50°-60°	266.7	5.6
60°-70°	213.6	4.4
70°-80°	122.8	2.6
80°-90°	33.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3330.0	69.3
0°-40°	3898.2	81.2
0°-60°	4433.3	92.3
0°-90°	4803.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4803.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5400	
5°	5220	492
15°	4855	1350
25°	3196	1487
35°	723	568
45°	350	268
55°	299	267
65°	217	214
75°	116	123
85°	28	33
90°	0	



TEST NUMBER: P793666

CATALOG NUMBER: LER6D50D010-EC6DR7040509040-6LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5399.9
2.5°	5343.5
5°	5219.5
7.5°	5116.1
10°	5016.1
12.5°	4931.4
15°	4855.3
17.5°	4671.5
20°	4410.8
22.5°	3848.2
25°	3195.8
27.5°	2782.0
30°	2158.8
32.5°	1394.4
35°	723.3
37.5°	390.7
40°	355.7
42.5°	353.1
45°	349.7
47.5°	342.0
50°	329.2
52.5°	314.6
55°	299.2
57.5°	282.1
60°	262.5
62.5°	240.2
65°	217.2
67.5°	191.5
70°	165.9
72.5°	140.2
75°	116.3
77.5°	91.5
80°	69.3
82.5°	48.7
85°	28.2
87.5°	11.1
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)