

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792615

Luminaire Tested: LER6D40BD010-EC6DR6040509050-6LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P792615  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D40BD010-EC6DR6040509050-6LBDP1B  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3766.2 lumens  
Efficiency: N/A  
Efficacy: 107.0 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 35.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P792615

CATALOG NUMBER: LER6D40BD010-EC6DR6040509050-6LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P792615

CATALOG NUMBER: LER6D40BD010-EC6DR6040509050-6LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	488712
5°	500735
10°	506780
15°	482775
20°	425663
25°	344284
30°	232885
35°	116697
40°	18927
45°	18527
50°	18902
55°	19182
60°	19711
65°	20166
70°	20637
75°	20896
80°	20135
85°	16799

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 20896 cd/sqm



TEST NUMBER: P792615

CATALOG NUMBER: LER6D40BD010-EC6DR6040509050-6LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	436.3	11.6
10°-20°	1180.6	31.3
20°-30°	1270.2	33.7
30°-40°	552.1	14.7
40°-50°	92.7	2.5
50°-60°	90.2	2.4
60°-70°	77.1	2.0
70°-80°	51.6	1.4
80°-90°	15.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2887.1	76.7
0°-40°	3439.2	91.3
0°-60°	3622.1	96.2
0°-90°	3766.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3766.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4473	
5°	4566	436
15°	4268	1181
25°	2856	1270
35°	875	552
45°	120	93
55°	101	90
65°	78	77
75°	50	52
85°	13	15
90°	0	



TEST NUMBER: P792615

CATALOG NUMBER: LER6D40BD010-EC6DR6040509050-6LBDP1B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4472.9
2.5°	4598.6
5°	4565.5
7.5°	4575.9
10°	4567.8
12.5°	4473.5
15°	4268.0
17.5°	3992.1
20°	3660.9
22.5°	3306.4
25°	2855.8
27.5°	2284.2
30°	1845.9
32.5°	1422.7
35°	874.9
37.5°	374.3
40°	132.7
42.5°	122.2
45°	119.9
47.5°	115.8
50°	111.2
52.5°	105.9
55°	100.7
57.5°	95.5
60°	90.2
62.5°	84.4
65°	78.0
67.5°	71.6
70°	64.6
72.5°	57.0
75°	49.5
77.5°	40.7
80°	32.0
82.5°	22.7
85°	13.4
87.5°	4.7
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)