

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794032

Luminaire Tested: LER6D55D010-EC6DR6055659030-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P794032
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D55D010-EC6DR6055659030-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6529.5 lumens
Efficiency: N/A
Efficacy: 112.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P794032
CATALOG NUMBER: LER6D55D010-EC6DR6055659030-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P794032

CATALOG NUMBER: LER6D55D010-EC6DR6055659030-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	847284
5°	868113
10°	878606
15°	836984
20°	737972
25°	596884
30°	403748
35°	202315
40°	32819
45°	32124
50°	32772
55°	33260
60°	34177
65°	34954
70°	35779
75°	36221
80°	34921
85°	29084

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 36221 cd/sqm



TEST NUMBER: P794032

CATALOG NUMBER: LER6D55D010-EC6DR6055659030-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	756.5	11.6
10°-20°	2046.7	31.3
20°-30°	2202.1	33.7
30°-40°	957.2	14.7
40°-50°	160.8	2.5
50°-60°	156.3	2.4
60°-70°	133.7	2.0
70°-80°	89.5	1.4
80°-90°	26.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5005.3	76.7
0°-40°	5962.5	91.3
0°-60°	6279.6	96.2
0°-90°	6529.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6529.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7755	
5°	7915	756
15°	7399	2047
25°	4951	2202
35°	1517	957
45°	208	161
55°	175	156
65°	135	134
75°	86	89
85°	23	27
90°	0	



TEST NUMBER: P794032

CATALOG NUMBER: LER6D55D010-EC6DR6055659030-6LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	7754.7
2.5°	7972.7
5°	7915.1
7.5°	7933.3
10°	7919.2
12.5°	7755.7
15°	7399.4
17.5°	6921.1
20°	6346.9
22.5°	5732.2
25°	4951.1
27.5°	3960.1
30°	3200.2
32.5°	2466.5
35°	1516.8
37.5°	648.9
40°	230.1
42.5°	211.9
45°	207.9
47.5°	200.8
50°	192.8
52.5°	183.7
55°	174.6
57.5°	165.5
60°	156.4
62.5°	146.3
65°	135.2
67.5°	124.1
70°	112.0
72.5°	98.9
75°	85.8
77.5°	70.6
80°	55.5
82.5°	39.4
85°	23.2
87.5°	8.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)