

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794087

Luminaire Tested: LER6D55D010-EC6DR6555659035-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P794087
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D55D010-EC6DR6555659035-6LBDDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4294.6 lumens
Efficiency: N/A
Efficacy: 73.8 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P794087
CATALOG NUMBER: LER6D55D010-EC6DR6555659035-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P794087

CATALOG NUMBER: LER6D55D010-EC6DR6555659035-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	461998
5°	462370
10°	478656
15°	479449
20°	441407
25°	376098
30°	287918
35°	203409
40°	120066
45°	48750
50°	17678
55°	9848
60°	5638
65°	3102
70°	3258
75°	2533
80°	2643
85°	2257

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 48750 cd/sqm



TEST NUMBER: P794087

CATALOG NUMBER: LER6D55D010-EC6DR6555659035-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	407.2	9.5
10°-20°	1174.5	27.3
20°-30°	1409.1	32.8
30°-40°	947.0	22.1
40°-50°	283.5	6.6
50°-60°	50.0	1.2
60°-70°	14.2	0.3
70°-80°	7.0	0.2
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2990.7	69.6
0°-40°	3937.7	91.7
0°-60°	4271.2	99.5
0°-90°	4294.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4294.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4228	
5°	4216	407
15°	4239	1174
25°	3120	1409
35°	1525	947
45°	316	283
55°	52	50
65°	12	14
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P794087

CATALOG NUMBER: LER6D55D010-EC6DR6555659035-6LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	4228.4
2.5°	4246.4
5°	4215.7
7.5°	4279.4
10°	4314.3
12.5°	4305.9
15°	4238.6
17.5°	4073.9
20°	3796.3
22.5°	3469.5
25°	3119.7
27.5°	2725.0
30°	2282.1
32.5°	1880.7
35°	1525.0
37.5°	1173.5
40°	841.8
42.5°	549.8
45°	315.5
47.5°	167.0
50°	104.0
52.5°	72.1
55°	51.7
57.5°	37.3
60°	25.8
62.5°	16.8
65°	12.0
67.5°	10.8
70°	10.2
72.5°	7.8
75°	6.0
77.5°	5.4
80°	4.2
82.5°	3.0
85°	1.8
87.5°	1.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)