

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792670

Luminaire Tested: LER6D40BD010-EC6DR6540509050-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P792670
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D40BD010-EC6DR6540509050-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4180.0 lumens
Efficiency: N/A
Efficacy: 118.8 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P792670
CATALOG NUMBER: LER6D40BD010-EC6DR6540509050-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P792670

CATALOG NUMBER: LER6D40BD010-EC6DR6540509050-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72		
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66		
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61		
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49		
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	221660
5°	221100
10°	220911
15°	214104
20°	194915
25°	169855
30°	141271
35°	111938
40°	80792
45°	51044
50°	26604
55°	14143
60°	7429
65°	4091
70°	1708
75°	1896
80°	1312
85°	1139

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 51044 cd/sqm



TEST NUMBER: P792670

CATALOG NUMBER: LER6D40BD010-EC6DR6540509050-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	358.9	8.6
10°-20°	982.9	23.5
20°-30°	1201.4	28.7
30°-40°	974.8	23.3
40°-50°	485.8	11.6
50°-60°	135.5	3.2
60°-70°	30.8	0.7
70°-80°	8.0	0.2
80°-90°	2.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2543.1	60.8
0°-40°	3517.9	84.2
0°-60°	4139.1	99.0
0°-90°	4180.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4180.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3795	
5°	3771	359
15°	3541	983
25°	2636	1201
35°	1570	975
45°	618	486
55°	139	135
65°	30	31
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P792670
CATALOG NUMBER: LER6D40BD010-EC6DR6540509050-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3795.3
2.5°	3792.5
5°	3771.3
7.5°	3759.0
10°	3725.0
12.5°	3655.9
15°	3541.0
17.5°	3361.4
20°	3136.1
22.5°	2892.9
25°	2635.8
27.5°	2360.8
30°	2094.8
32.5°	1832.1
35°	1570.0
37.5°	1308.4
40°	1059.7
42.5°	826.5
45°	618.0
47.5°	430.6
50°	292.8
52.5°	201.9
55°	138.9
57.5°	93.7
60°	63.6
62.5°	44.1
65°	29.6
67.5°	15.1
70°	10.0
72.5°	9.5
75°	8.4
77.5°	5.6
80°	3.9
82.5°	2.8
85°	1.7
87.5°	1.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)