

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794106

Luminaire Tested: LER6D55D010-EC6DR6555659050-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P794106
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D55D010-EC6DR6555659050-6LB DP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5244.1 lumens
Efficiency: N/A
Efficacy: 90.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P794106
CATALOG NUMBER: LER6D55D010-EC6DR6555659050-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P794106

CATALOG NUMBER: LER6D55D010-EC6DR6555659050-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	564135
5°	564601
10°	584476
15°	585450
20°	539006
25°	459258
30°	351580
35°	248385
40°	146609
45°	59520
50°	21570
55°	12020
60°	6905
65°	3800
70°	3993
75°	3082
80°	3209
85°	2758

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 59520 cd/sqm



TEST NUMBER: P794106

CATALOG NUMBER: LER6D55D010-EC6DR6555659050-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	497.2	9.5
10°-20°	1434.1	27.3
20°-30°	1720.7	32.8
30°-40°	1156.4	22.1
40°-50°	346.2	6.6
50°-60°	61.1	1.2
60°-70°	17.4	0.3
70°-80°	8.5	0.2
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3652.0	69.6
0°-40°	4808.3	91.7
0°-60°	5215.6	99.5
0°-90°	5244.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5244.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5163	
5°	5148	497
15°	5176	1434
25°	3810	1721
35°	1862	1156
45°	385	346
55°	63	61
65°	15	17
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P794106

CATALOG NUMBER: LER6D55D010-EC6DR6555659050-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5163.2
2.5°	5185.2
5°	5147.8
7.5°	5225.6
10°	5268.1
12.5°	5257.9
15°	5175.7
17.5°	4974.6
20°	4635.7
22.5°	4236.5
25°	3809.5
27.5°	3327.4
30°	2786.7
32.5°	2296.6
35°	1862.2
37.5°	1433.0
40°	1027.9
42.5°	671.4
45°	385.2
47.5°	204.0
50°	126.9
52.5°	88.0
55°	63.1
57.5°	45.5
60°	31.6
62.5°	20.5
65°	14.7
67.5°	13.2
70°	12.5
72.5°	9.5
75°	7.3
77.5°	6.6
80°	5.1
82.5°	3.7
85°	2.2
87.5°	1.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)