

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792687

Luminaire Tested: LER6D40BD010-EC6DR7040509030-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P792687
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D40BD010-EC6DR7040509030-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2629.1 lumens
Efficiency: N/A
Efficacy: 74.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P792687

CATALOG NUMBER: LER6D40BD010-EC6DR7040509030-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P792687

CATALOG NUMBER: LER6D40BD010-EC6DR7040509030-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	322964
5°	313372
10°	304636
15°	300637
20°	280729
25°	210900
30°	149087
35°	52806
40°	27770
45°	29575
50°	30630
55°	31202
60°	31402
65°	30740
70°	29007
75°	26849
80°	23847
85°	19306

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 31402 cd/sqm



TEST NUMBER: P792687

CATALOG NUMBER: LER6D40BD010-EC6DR7040509030-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	269.5	10.3
10°-20°	739.2	28.1
20°-30°	814.1	31.0
30°-40°	311.1	11.8
40°-50°	146.9	5.6
50°-60°	146.0	5.6
60°-70°	116.9	4.4
70°-80°	67.2	2.6
80°-90°	18.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1822.8	69.3
0°-40°	2133.9	81.2
0°-60°	2426.8	92.3
0°-90°	2629.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2629.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2956	
5°	2857	269
15°	2658	739
25°	1749	814
35°	396	311
45°	191	147
55°	164	146
65°	119	117
75°	64	67
85°	15	18
90°	0	



TEST NUMBER: P792687

CATALOG NUMBER: LER6D40BD010-EC6DR7040509030-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2955.9
2.5°	2925.0
5°	2857.2
7.5°	2800.6
10°	2745.8
12.5°	2699.5
15°	2657.8
17.5°	2557.2
20°	2414.4
22.5°	2106.5
25°	1749.4
27.5°	1522.9
30°	1181.7
32.5°	763.3
35°	395.9
37.5°	213.9
40°	194.7
42.5°	193.3
45°	191.4
47.5°	187.2
50°	180.2
52.5°	172.2
55°	163.8
57.5°	154.4
60°	143.7
62.5°	131.5
65°	118.9
67.5°	104.8
70°	90.8
72.5°	76.8
75°	63.6
77.5°	50.1
80°	37.9
82.5°	26.7
85°	15.4
87.5°	6.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)