

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794127

Luminaire Tested: LER6D55D010-EC6DR7055659030-6LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P794127  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D55D010-EC6DR7055659030-6LBDDP1B  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3824.0 lumens  
Efficiency: N/A  
Efficacy: 65.7 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 58.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P794127  
CATALOG NUMBER: LER6D55D010-EC6DR7055659030-6LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P794127

CATALOG NUMBER: LER6D55D010-EC6DR7055659030-6LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	469734
5°	455778
10°	443075
15°	437258
20°	408315
25°	306742
30°	216837
35°	76815
40°	40393
45°	43018
50°	44552
55°	45375
60°	45671
65°	44700
70°	42200
75°	39091
80°	34669
85°	28207

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 45673 cd/sqm



TEST NUMBER: P794127

CATALOG NUMBER: LER6D55D010-EC6DR7055659030-6LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	392.0	10.3
10°-20°	1075.1	28.1
20°-30°	1184.1	31.0
30°-40°	452.4	11.8
40°-50°	213.6	5.6
50°-60°	212.4	5.6
60°-70°	170.1	4.4
70°-80°	97.7	2.6
80°-90°	26.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2651.2	69.3
0°-40°	3103.6	81.2
0°-60°	3529.6	92.3
0°-90°	3824.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3824.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4299	
5°	4156	392
15°	3866	1075
25°	2544	1184
35°	576	452
45°	278	214
55°	238	212
65°	173	170
75°	93	98
85°	22	27
90°	0	



TEST NUMBER: P794127

CATALOG NUMBER: LER6D55D010-EC6DR7055659030-6LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4299.2
2.5°	4254.3
5°	4155.6
7.5°	4073.2
10°	3993.6
12.5°	3926.2
15°	3865.6
17.5°	3719.3
20°	3511.7
22.5°	3063.8
25°	2544.4
27.5°	2215.0
30°	1718.7
32.5°	1110.2
35°	575.9
37.5°	311.1
40°	283.2
42.5°	281.1
45°	278.4
47.5°	272.3
50°	262.1
52.5°	250.5
55°	238.2
57.5°	224.6
60°	209.0
62.5°	191.3
65°	172.9
67.5°	152.5
70°	132.1
72.5°	111.6
75°	92.6
77.5°	72.8
80°	55.1
82.5°	38.8
85°	22.5
87.5°	8.8
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)