

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792696

Luminaire Tested: LER6D40BD010-EC6DR7040509035-6LBDP1H

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P792696  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D40BD010-EC6DR7040509035-6LBDP1H  
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4566.4 lumens  
Efficiency: N/A  
Efficacy: 129.7 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 35.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P792696

CATALOG NUMBER: LER6D40BD010-EC6DR7040509035-6LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P792696

CATALOG NUMBER: LER6D40BD010-EC6DR7040509035-6LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	560945
5°	544278
10°	529103
15°	522162
20°	487590
25°	366309
30°	258950
35°	91727
40°	48223
45°	51377
50°	53187
55°	54194
60°	54521
65°	53387
70°	50378
75°	46648
80°	41402
85°	33597

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 54539 cd/sqm



TEST NUMBER: P792696

CATALOG NUMBER: LER6D40BD010-EC6DR7040509035-6LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	468.1	10.3
10°-20°	1283.9	28.1
20°-30°	1414.0	31.0
30°-40°	540.3	11.8
40°-50°	255.1	5.6
50°-60°	253.6	5.6
60°-70°	203.1	4.4
70°-80°	116.7	2.6
80°-90°	31.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3166.0	69.3
0°-40°	3706.3	81.2
0°-60°	4214.9	92.3
0°-90°	4566.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4566.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5134	
5°	4962	468
15°	4616	1284
25°	3038	1414
35°	688	540
45°	332	255
55°	284	254
65°	206	203
75°	110	117
85°	27	32
90°	0	



TEST NUMBER: P792696

CATALOG NUMBER: LER6D40BD010-EC6DR7040509035-6LBDP1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5134.0
2.5°	5080.3
5°	4962.5
7.5°	4864.1
10°	4769.0
12.5°	4688.5
15°	4616.2
17.5°	4441.4
20°	4193.5
22.5°	3658.7
25°	3038.5
27.5°	2645.0
30°	2052.5
32.5°	1325.8
35°	687.7
37.5°	371.5
40°	338.1
42.5°	335.7
45°	332.5
47.5°	325.1
50°	312.9
52.5°	299.1
55°	284.5
57.5°	268.2
60°	249.5
62.5°	228.4
65°	206.5
67.5°	182.1
70°	157.7
72.5°	133.3
75°	110.5
77.5°	87.0
80°	65.8
82.5°	46.3
85°	26.8
87.5°	10.6
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)