

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794152

Luminaire Tested: LER6D55D010-EC6DR7055659050-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P794152
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D55D010-EC6DR7055659050-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7001.8 lumens
Efficiency: N/A
Efficacy: 120.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P794152
CATALOG NUMBER: LER6D55D010-EC6DR7055659050-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P794152

CATALOG NUMBER: LER6D55D010-EC6DR7055659050-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	860101
5°	834541
10°	811284
15°	800640
20°	747635
25°	561658
30°	397049
35°	140639
40°	73954
45°	78773
50°	81556
55°	83092
60°	83606
65°	81852
70°	77245
75°	71555
80°	63550
85°	51524

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 83639 cd/sqm



TEST NUMBER: P794152

CATALOG NUMBER: LER6D55D010-EC6DR7055659050-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	717.7	10.3
10°-20°	1968.6	28.1
20°-30°	2168.2	31.0
30°-40°	828.4	11.8
40°-50°	391.1	5.6
50°-60°	388.9	5.6
60°-70°	311.3	4.4
70°-80°	179.0	2.6
80°-90°	48.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4854.5	69.3
0°-40°	5682.9	81.2
0°-60°	6462.8	92.3
0°-90°	7001.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7001.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7872	
5°	7609	718
15°	7078	1969
25°	4659	2168
35°	1054	828
45°	510	391
55°	436	389
65°	317	311
75°	170	179
85°	41	49
90°	0	



TEST NUMBER: P794152

CATALOG NUMBER: LER6D55D010-EC6DR7055659050-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	7872.0
2.5°	7789.8
5°	7609.0
7.5°	7458.2
10°	7312.4
12.5°	7189.0
15°	7078.1
17.5°	6810.1
20°	6430.0
22.5°	5609.9
25°	4658.9
27.5°	4055.7
30°	3147.1
32.5°	2032.8
35°	1054.4
37.5°	569.6
40°	518.5
42.5°	514.7
45°	509.8
47.5°	498.5
50°	479.8
52.5°	458.7
55°	436.2
57.5°	411.3
60°	382.6
62.5°	350.2
65°	316.6
67.5°	279.2
70°	241.8
72.5°	204.4
75°	169.5
77.5°	133.4
80°	101.0
82.5°	71.0
85°	41.1
87.5°	16.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)