

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792704

Luminaire Tested: LER6D40BD010-EC6DR7040509040-6LBDP1H

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P792704  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D40BD010-EC6DR7040509040-6LBDP1H  
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4779.9 lumens  
Efficiency: N/A  
Efficacy: 135.8 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 35.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P792704

CATALOG NUMBER: LER6D40BD010-EC6DR7040509040-6LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P792704

CATALOG NUMBER: LER6D40BD010-EC6DR7040509040-6LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	587167
5°	569723
10°	553844
15°	546572
20°	510391
25°	383428
30°	271050
35°	96009
40°	50491
45°	53772
50°	55685
55°	56728
60°	57078
65°	55869
70°	52742
75°	48843
80°	43352
85°	35227

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 57101 cd/sqm



TEST NUMBER: P792704

CATALOG NUMBER: LER6D40BD010-EC6DR7040509040-6LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	489.9	10.3
10°-20°	1343.9	28.1
20°-30°	1480.1	31.0
30°-40°	565.5	11.8
40°-50°	267.0	5.6
50°-60°	265.5	5.6
60°-70°	212.5	4.4
70°-80°	122.1	2.6
80°-90°	33.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3314.0	69.3
0°-40°	3879.5	81.2
0°-60°	4412.0	92.3
0°-90°	4779.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4779.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5374	
5°	5194	490
15°	4832	1344
25°	3180	1480
35°	720	566
45°	348	267
55°	298	265
65°	216	213
75°	116	122
85°	28	33
90°	0	



TEST NUMBER: P792704

CATALOG NUMBER: LER6D40BD010-EC6DR7040509040-6LBDP1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5374.0
2.5°	5317.9
5°	5194.5
7.5°	5091.5
10°	4992.0
12.5°	4907.7
15°	4832.0
17.5°	4649.1
20°	4389.6
22.5°	3829.7
25°	3180.5
27.5°	2768.7
30°	2148.4
32.5°	1387.7
35°	719.8
37.5°	388.8
40°	354.0
42.5°	351.4
45°	348.0
47.5°	340.3
50°	327.6
52.5°	313.1
55°	297.8
57.5°	280.8
60°	261.2
62.5°	239.1
65°	216.1
67.5°	190.6
70°	165.1
72.5°	139.5
75°	115.7
77.5°	91.0
80°	68.9
82.5°	48.5
85°	28.1
87.5°	11.1
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)