

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794208

Luminaire Tested: LER6D60D010-EC6DR3055659024-6LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P794208
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D60D010-EC6DR3055659024-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5991.3 lumens
Efficiency: N/A
Efficacy: 93.0 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P794208
CATALOG NUMBER: LER6D60D010-EC6DR3055659024-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P794208

CATALOG NUMBER: LER6D60D010-EC6DR3055659024-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1474586	1474586	1474586
5°	1432257	1430582	1432326
10°	1240548	1231804	1240261
15°	809402	805051	801002
20°	402473	417575	401935
25°	202737	228623	198582
30°	81173	88447	70725
35°	37648	36059	30229
40°	16257	18056	15308
45°	11464	14235	11572
50°	3942	10360	4168
55°	2269	4297	2402
60°	1592	1883	1592
65°	1032	1032	1032
70°	627	425	627
75°	0	266	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 14235 cd/sqm



TEST NUMBER: P794208

CATALOG NUMBER: LER6D60D010-EC6DR3055659024-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1694.0	28.3
10°-20°	2728.3	45.5
20°-30°	1179.0	19.7
30°-40°	268.7	4.5
40°-50°	92.3	1.5
50°-60°	22.5	0.4
60°-70°	5.9	0.1
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5601.3	93.5
0°-40°	5870.0	98.0
0°-60°	5984.8	99.9
0°-90°	5991.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5991.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	19265	19265	19265	19265	19265	
5°	18640	18622	18619	18658	18641	1695
15°	10214	10091	10159	10126	10108	2735
25°	2400	2491	2707	2428	2351	1149
35°	403	411	386	383	324	273
45°	106	132	132	132	107	75
55°	17	18	32	19	18	17
65°	6	6	6	6	6	6
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P794208

CATALOG NUMBER: LER6D60D010-EC6DR3055659024-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	19264.7	19264.7	19264.7	19264.7	19264.7
2.5°	19137.0	19123.8	19131.4	19140.8	19144.6
5°	18640.5	18622.5	18618.7	18657.5	18641.4
7.5°	17638.8	17613.3	17574.5	17662.5	17744.8
10°	15960.9	15932.6	15848.4	15890.0	15957.2
12.5°	13483.8	13392.1	13390.2	13522.6	13504.6
15°	10214.1	10091.1	10159.2	10126.1	10108.1
17.5°	6868.6	6821.4	6912.2	6884.7	6766.5
20°	4941.0	4953.3	5126.4	5039.4	4934.4
22.5°	3605.5	3650.0	3855.2	3631.1	3548.8
25°	2400.5	2491.3	2707.0	2428.0	2351.3
27.5°	1476.4	1518.1	1736.6	1457.5	1415.9
30°	918.4	897.6	1000.7	858.8	800.2
32.5°	602.5	576.0	609.1	546.7	499.4
35°	402.9	411.4	385.9	383.1	323.5
37.5°	251.6	289.4	255.4	272.4	208.1
40°	162.7	210.0	180.7	199.6	153.2
42.5°	133.4	161.7	148.5	158.0	136.2
45°	105.9	131.5	131.5	131.5	106.9
47.5°	58.6	88.0	112.6	89.9	62.4
50°	33.1	44.5	87.0	46.3	35.0
52.5°	22.7	25.5	59.6	26.5	23.6
55°	17.0	18.0	32.2	18.9	18.0
57.5°	13.2	14.2	17.0	14.2	13.2
60°	10.4	10.4	12.3	11.4	10.4
62.5°	7.6	7.6	8.5	7.6	7.6
65°	5.7	5.7	5.7	5.7	5.7
67.5°	2.8	3.8	3.8	3.8	3.8
70°	2.8	1.9	1.9	1.9	2.8
72.5°	1.9	0.9	0.9	0.9	0.9
75°	0.0	0.0	0.9	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)