

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794413

Luminaire Tested: LER6D60D010-EC6DR5055659027-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P794413
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D60D010-EC6DR5055659027-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7968.4 lumens
Efficiency: N/A
Efficacy: 123.7 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P794413
CATALOG NUMBER: LER6D60D010-EC6DR5055659027-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P794413

CATALOG NUMBER: LER6D60D010-EC6DR5055659027-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 | | | | | | | | | | | | | | | | |
| 1 | 114 | 112 | 109 | 107 | 112 | 110 | 108 | 106 | 106 | 104 | 102 | 102 | 101 | 99 | 98 | 97 | 97 | 95 | | | 95 | | | | | | | | | | | | | | | | |
| 2 | 109 | 105 | 101 | 98 | 107 | 103 | 100 | 97 | 100 | 98 | 95 | 97 | 95 | 93 | 95 | 93 | 91 | 90 | | | 90 | | | | | | | | | | | | | | | | |
| 3 | 105 | 99 | 95 | 91 | 103 | 98 | 94 | 90 | 95 | 92 | 89 | 93 | 90 | 88 | 91 | 88 | 86 | 85 | | | 85 | | | | | | | | | | | | | | | | |
| 4 | 100 | 94 | 89 | 85 | 99 | 93 | 88 | 85 | 90 | 87 | 84 | 89 | 85 | 83 | 87 | 84 | 82 | 80 | | | 80 | | | | | | | | | | | | | | | | |
| 5 | 96 | 89 | 84 | 80 | 95 | 88 | 83 | 79 | 86 | 82 | 79 | 85 | 81 | 78 | 83 | 80 | 77 | 76 | | | 76 | | | | | | | | | | | | | | | | |
| 6 | 92 | 84 | 79 | 75 | 91 | 83 | 79 | 75 | 82 | 78 | 74 | 81 | 77 | 74 | 79 | 76 | 74 | 72 | | | 72 | | | | | | | | | | | | | | | | |
| 7 | 88 | 80 | 75 | 71 | 87 | 79 | 74 | 71 | 78 | 74 | 71 | 77 | 73 | 70 | 76 | 73 | 70 | 69 | | | 69 | | | | | | | | | | | | | | | | |
| 8 | 85 | 76 | 71 | 67 | 84 | 76 | 71 | 67 | 75 | 70 | 67 | 74 | 70 | 67 | 73 | 69 | 66 | 65 | | | 65 | | | | | | | | | | | | | | | | |
| 9 | 81 | 73 | 68 | 64 | 80 | 72 | 67 | 64 | 71 | 67 | 64 | 71 | 67 | 64 | 70 | 66 | 63 | 62 | | | 62 | | | | | | | | | | | | | | | | |
| 10 | 78 | 70 | 64 | 61 | 77 | 69 | 64 | 61 | 68 | 64 | 61 | 68 | 64 | 61 | 67 | 63 | 60 | 59 | | | 59 | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 1402810 |
| 5° | 1388108 |
| 10° | 1365238 |
| 15° | 1243157 |
| 20° | 1034456 |
| 25° | 734306 |
| 30° | 388672 |
| 35° | 158392 |
| 40° | 58821 |
| 45° | 26932 |
| 50° | 11032 |
| 55° | 5772 |
| 60° | 2841 |
| 65° | 827 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 26932 cd/sqm



TEST NUMBER: P794413

CATALOG NUMBER: LER6D60D010-EC6DR5055659027-6LBS1LI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 1196.3 | 15.0 |
| 10°-20° | 3023.2 | 37.9 |
| 20°-30° | 2715.6 | 34.1 |
| 30°-40° | 850.3 | 10.7 |
| 40°-50° | 148.9 | 1.9 |
| 50°-60° | 29.7 | 0.4 |
| 60°-70° | 4.5 | 0.1 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 6935.1 | 87.0 |
| 0°-40° | 7785.4 | 97.7 |
| 0°-60° | 7963.9 | 99.9 |
| 0°-90° | 7968.4 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 7968.4 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-------|------|
| 0° | 12839 | |
| 5° | 12656 | ### |
| 15° | 10990 | 3023 |
| 25° | 6091 | 2716 |
| 35° | 1188 | 850 |
| 45° | 174 | 149 |
| 55° | 30 | 30 |
| 65° | 3 | 4 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P794413

CATALOG NUMBER: LER6D60D010-EC6DR5055659027-6LBS1LI

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|---------|
| 0° | 12839.1 |
| 2.5° | 12775.2 |
| 5° | 12656.2 |
| 7.5° | 12474.3 |
| 10° | 12305.4 |
| 12.5° | 11764.2 |
| 15° | 10990.2 |
| 17.5° | 10007.4 |
| 20° | 8896.8 |
| 22.5° | 7611.9 |
| 25° | 6091.0 |
| 27.5° | 4478.1 |
| 30° | 3080.7 |
| 32.5° | 2005.8 |
| 35° | 1187.5 |
| 37.5° | 682.0 |
| 40° | 412.4 |
| 42.5° | 268.5 |
| 45° | 174.3 |
| 47.5° | 106.1 |
| 50° | 64.9 |
| 52.5° | 44.4 |
| 55° | 30.3 |
| 57.5° | 20.6 |
| 60° | 13.0 |
| 62.5° | 7.6 |
| 65° | 3.2 |
| 67.5° | 1.1 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)