

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792913

Luminaire Tested: LER6D45BD010-EC6DR4540509024-6LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P792913
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D45BD010-EC6DR4540509024-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4518.8 lumens
Efficiency: N/A
Efficacy: 116.8 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P792913

CATALOG NUMBER: LER6D45BD010-EC6DR4540509024-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P792913
 CATALOG NUMBER: LER6D45BD010-EC6DR4540509024-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	97	97	97	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	91	91	91	90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	87	87	87	85
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	82	82	82	81
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	78	78	78	77
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	74	74	74	73
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	71	71	71	69
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	67	67	67	66
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	64	64	64	63
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	61	61	61	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	872687
5°	847834
10°	811150
15°	742374
20°	588957
25°	367696
30°	202669
35°	90994
40°	35843
45°	16889
50°	8006
55°	4191
60°	2054
65°	491
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16889 cd/sqm



TEST NUMBER: P792913

CATALOG NUMBER: LER6D45BD010-EC6DR4540509024-6LBDP1LI

ZONAL LUMENS:

CANDELA DISTRIBUTION:

Zone	Lumens	% Fixture
0°-10°	726.3	16.1
10°-20°	1787.6	39.6
20°-30°	1415.6	31.3
30°-40°	471.4	10.4
40°-50°	93.6	2.1
50°-60°	21.2	0.5
60°-70°	3.0	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3929.5	87.0
0°-40°	4400.9	97.4
0°-60°	4515.7	99.9
0°-90°	4518.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4518.8	100.0

	0°	Flux
0°	7987	
5°	7730	726
15°	6563	1788
25°	3050	1416
35°	682	471
45°	109	94
55°	22	21
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P792913

CATALOG NUMBER: LER6D45BD010-EC6DR4540509024-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	7987.2
2.5°	7935.0
5°	7730.2
7.5°	7561.2
10°	7311.2
12.5°	6978.3
15°	6563.0
17.5°	5938.6
20°	5065.3
22.5°	4025.0
25°	3050.0
27.5°	2233.3
30°	1606.4
32.5°	1092.5
35°	682.2
37.5°	404.6
40°	251.3
42.5°	165.2
45°	109.3
47.5°	70.4
50°	47.1
52.5°	31.4
55°	22.0
57.5°	14.4
60°	9.4
62.5°	5.0
65°	1.9
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)