

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794498

Luminaire Tested: LER6D60D010-EC6DR6055659024-6LBDP1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P794498  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D60D010-EC6DR6055659024-6LB DP1MW  
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5571.9 lumens  
Efficiency: N/A  
Efficacy: 86.5 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 64.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P794498  
CATALOG NUMBER: LER6D60D010-EC6DR6055659024-6LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P794498

CATALOG NUMBER: LER6D60D010-EC6DR6055659024-6LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93															
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86				86															
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80				80															
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75				75															
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70				70															
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66				66															
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62				62															
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59				59															
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55				55															
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53				53															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	723011
5°	740788
10°	749742
15°	714231
20°	629734
25°	509337
30°	344527
35°	172651
40°	27998
45°	27412
50°	27962
55°	28383
60°	29173
65°	29835
70°	30540
75°	30901
80°	29824
85°	24822

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 30901 cd/sqm



TEST NUMBER: P794498

CATALOG NUMBER: LER6D60D010-EC6DR6055659024-6LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	645.5	11.6
10°-20°	1746.5	31.3
20°-30°	1879.1	33.7
30°-40°	816.8	14.7
40°-50°	137.2	2.5
50°-60°	133.4	2.4
60°-70°	114.1	2.0
70°-80°	76.4	1.4
80°-90°	22.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4271.2	76.7
0°-40°	5088.0	91.3
0°-60°	5358.6	96.2
0°-90°	5571.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5571.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6617	
5°	6754	646
15°	6314	1747
25°	4225	1879
35°	1294	817
45°	177	137
55°	149	133
65°	115	114
75°	73	76
85°	20	23
90°	0	



TEST NUMBER: P794498

CATALOG NUMBER: LER6D60D010-EC6DR6055659024-6LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6617.3
2.5°	6803.3
5°	6754.2
7.5°	6769.7
10°	6757.7
12.5°	6618.2
15°	6314.2
17.5°	5906.0
20°	5416.0
22.5°	4891.5
25°	4224.9
27.5°	3379.3
30°	2730.8
32.5°	2104.7
35°	1294.4
37.5°	553.7
40°	196.3
42.5°	180.8
45°	177.4
47.5°	171.4
50°	164.5
52.5°	156.7
55°	149.0
57.5°	141.2
60°	133.5
62.5°	124.9
65°	115.4
67.5°	105.9
70°	95.6
72.5°	84.4
75°	73.2
77.5°	60.3
80°	47.4
82.5°	33.6
85°	19.8
87.5°	6.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)