

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794537

Luminaire Tested: LER6D60D010-EC6DR6055659050-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P794537
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D60D010-EC6DR6055659050-6LBDDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8031.8 lumens
Efficiency: N/A
Efficacy: 124.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P794537
CATALOG NUMBER: LER6D60D010-EC6DR6055659050-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P794537

CATALOG NUMBER: LER6D60D010-EC6DR6055659050-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1042206
5°	1067837
10°	1080739
15°	1029551
20°	907742
25°	734210
30°	496630
35°	248866
40°	40364
45°	39510
50°	40302
55°	40917
60°	42044
65°	42994
70°	44021
75°	44537
80°	42975
85°	35854

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 44537 cd/sqm



TEST NUMBER: P794537

CATALOG NUMBER: LER6D60D010-EC6DR6055659050-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	930.5	11.6
10°-20°	2517.6	31.3
20°-30°	2708.7	33.7
30°-40°	1177.4	14.7
40°-50°	197.7	2.5
50°-60°	192.3	2.4
60°-70°	164.5	2.0
70°-80°	110.1	1.4
80°-90°	32.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6156.9	76.7
0°-40°	7334.3	91.3
0°-60°	7724.3	96.2
0°-90°	8031.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8031.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9539	
5°	9736	931
15°	9102	2518
25°	6090	2709
35°	1866	1177
45°	256	198
55°	215	192
65°	166	164
75°	106	110
85°	29	33
90°	0	



TEST NUMBER: P794537

CATALOG NUMBER: LER6D60D010-EC6DR6055659050-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	9538.7
2.5°	9806.9
5°	9736.1
7.5°	9758.4
10°	9741.1
12.5°	9540.0
15°	9101.8
17.5°	8513.3
20°	7807.0
22.5°	7051.0
25°	6090.2
27.5°	4871.2
30°	3936.4
32.5°	3033.9
35°	1865.8
37.5°	798.2
40°	283.0
42.5°	260.7
45°	255.7
47.5°	247.0
50°	237.1
52.5°	225.9
55°	214.8
57.5°	203.6
60°	192.4
62.5°	180.0
65°	166.3
67.5°	152.7
70°	137.8
72.5°	121.7
75°	105.5
77.5°	86.9
80°	68.3
82.5°	48.4
85°	28.6
87.5°	9.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)