

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794538

Luminaire Tested: LER6D60D010-EC6DR6055659050-6LBDP1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P794538  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D60D010-EC6DR6055659050-6LBDP1MW  
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6927.3 lumens  
Efficiency: N/A  
Efficacy: 107.6 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 64.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P794538

CATALOG NUMBER: LER6D60D010-EC6DR6055659050-6LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P794538

CATALOG NUMBER: LER6D60D010-EC6DR6055659050-6LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	898888
5°	920989
10°	932115
15°	887965
20°	782912
25°	633244
30°	428338
35°	214640
40°	34816
45°	34087
50°	34761
55°	35279
60°	36275
65°	37099
70°	37952
75°	38416
80°	37060
85°	30839

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 38416 cd/sqm



TEST NUMBER: P794538

CATALOG NUMBER: LER6D60D010-EC6DR6055659050-6LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	802.6	11.6
10°-20°	2171.4	31.3
20°-30°	2336.2	33.7
30°-40°	1015.5	14.7
40°-50°	170.6	2.5
50°-60°	165.9	2.4
60°-70°	141.8	2.0
70°-80°	94.9	1.4
80°-90°	28.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5310.2	76.7
0°-40°	6325.7	91.3
0°-60°	6662.1	96.2
0°-90°	6927.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6927.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8227	
5°	8397	803
15°	7850	2171
25°	5253	2336
35°	1609	1016
45°	221	171
55°	185	166
65°	144	142
75°	91	95
85°	25	28
90°	0	



TEST NUMBER: P794538

CATALOG NUMBER: LER6D60D010-EC6DR6055659050-6LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	8227.0
2.5°	8458.3
5°	8397.2
7.5°	8416.5
10°	8401.5
12.5°	8228.1
15°	7850.1
17.5°	7342.6
20°	6733.4
22.5°	6081.4
25°	5252.7
27.5°	4201.3
30°	3395.1
32.5°	2616.7
35°	1609.2
37.5°	688.4
40°	244.1
42.5°	224.8
45°	220.6
47.5°	213.1
50°	204.5
52.5°	194.9
55°	185.2
57.5°	175.6
60°	166.0
62.5°	155.2
65°	143.5
67.5°	131.7
70°	118.8
72.5°	104.9
75°	91.0
77.5°	74.9
80°	58.9
82.5°	41.8
85°	24.6
87.5°	8.6
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)