

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793064

Luminaire Tested: LER6D45BD010-EC6DR6040509027-6LBDP1H

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P793064  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D45BD010-EC6DR6040509027-6LBDP1H  
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4773.4 lumens  
Efficiency: N/A  
Efficacy: 123.3 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 38.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P793064

CATALOG NUMBER: LER6D45BD010-EC6DR6040509027-6LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P793064

CATALOG NUMBER: LER6D45BD010-EC6DR6040509027-6LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	619399
5°	634630
10°	642301
15°	611873
20°	539483
25°	436352
30°	295159
35°	147908
40°	23990
45°	23487
50°	23950
55°	24307
60°	24999
65°	25569
70°	26164
75°	26469
80°	25546
85°	21312

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 26469 cd/sqm



TEST NUMBER: P793064

CATALOG NUMBER: LER6D45BD010-EC6DR6040509027-6LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	553.0	11.6
10°-20°	1496.2	31.3
20°-30°	1609.8	33.7
30°-40°	699.8	14.7
40°-50°	117.5	2.5
50°-60°	114.3	2.4
60°-70°	97.8	2.0
70°-80°	65.4	1.4
80°-90°	19.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3659.1	76.7
0°-40°	4358.9	91.3
0°-60°	4590.7	96.2
0°-90°	4773.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4773.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5669	
5°	5786	553
15°	5409	1496
25°	3620	1610
35°	1109	700
45°	152	118
55°	128	114
65°	99	98
75°	63	65
85°	17	20
90°	0	



TEST NUMBER: P793064

CATALOG NUMBER: LER6D45BD010-EC6DR6040509027-6LBDP1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5669.0
2.5°	5828.4
5°	5786.3
7.5°	5799.6
10°	5789.3
12.5°	5669.7
15°	5409.3
17.5°	5059.6
20°	4639.8
22.5°	4190.5
25°	3619.5
27.5°	2895.0
30°	2339.5
32.5°	1803.1
35°	1108.9
37.5°	474.4
40°	168.2
42.5°	154.9
45°	152.0
47.5°	146.8
50°	140.9
52.5°	134.3
55°	127.6
57.5°	121.0
60°	114.4
62.5°	107.0
65°	98.9
67.5°	90.7
70°	81.9
72.5°	72.3
75°	62.7
77.5°	51.6
80°	40.6
82.5°	28.8
85°	17.0
87.5°	5.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)