

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793073

Luminaire Tested: LER6D45BD010-EC6DR6040509030-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P793073
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D45BD010-EC6DR6040509030-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5163.5 lumens
Efficiency: N/A
Efficacy: 133.4 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P793073

CATALOG NUMBER: LER6D45BD010-EC6DR6040509030-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P793073

CATALOG NUMBER: LER6D45BD010-EC6DR6040509030-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	670020
5°	686497
10°	694790
15°	661881
20°	583574
25°	472013
30°	319282
35°	159993
40°	25959
45°	25403
50°	25905
55°	26307
60°	27031
65°	27637
70°	28304
75°	28622
80°	27622
85°	23067

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 28622 cd/sqm



TEST NUMBER: P793073

CATALOG NUMBER: LER6D45BD010-EC6DR6040509030-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	598.2	11.6
10°-20°	1618.5	31.3
20°-30°	1741.4	33.7
30°-40°	757.0	14.7
40°-50°	127.1	2.5
50°-60°	123.6	2.4
60°-70°	105.7	2.0
70°-80°	70.7	1.4
80°-90°	21.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3958.2	76.7
0°-40°	4715.1	91.3
0°-60°	4965.9	96.2
0°-90°	5163.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5163.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6132	
5°	6259	598
15°	5851	1619
25°	3915	1741
35°	1200	757
45°	164	127
55°	138	124
65°	107	106
75°	68	71
85°	18	21
90°	0	



TEST NUMBER: P793073

CATALOG NUMBER: LER6D45BD010-EC6DR6040509030-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	6132.3
2.5°	6304.7
5°	6259.2
7.5°	6273.6
10°	6262.4
12.5°	6133.1
15°	5851.4
17.5°	5473.1
20°	5019.0
22.5°	4533.0
25°	3915.3
27.5°	3131.6
30°	2530.7
32.5°	1950.5
35°	1199.5
37.5°	513.2
40°	182.0
42.5°	167.6
45°	164.4
47.5°	158.8
50°	152.4
52.5°	145.2
55°	138.1
57.5°	130.9
60°	123.7
62.5°	115.7
65°	106.9
67.5°	98.2
70°	88.6
72.5°	78.2
75°	67.8
77.5°	55.9
80°	43.9
82.5°	31.1
85°	18.4
87.5°	6.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)