

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794569

Luminaire Tested: LER6D60D010-EC6DR6555659035-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P794569
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D60D010-EC6DR6555659035-6LB DP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6656.9 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P794569
CATALOG NUMBER: LER6D60D010-EC6DR6555659035-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P794569

CATALOG NUMBER: LER6D60D010-EC6DR6555659035-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																												
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																												
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																												
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																												
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																												
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																												
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																												
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																												
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																												
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	716117
5°	716703
10°	741942
15°	743166
20°	684208
25°	582984
30°	446291
35°	315303
40°	186118
45°	75559
50°	27384
55°	15258
60°	8741
65°	4809
70°	5047
75°	3926
80°	4090
85°	3510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 75559 cd/sqm



TEST NUMBER: P794569

CATALOG NUMBER: LER6D60D010-EC6DR6555659035-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	631.1	9.5
10°-20°	1820.5	27.3
20°-30°	2184.2	32.8
30°-40°	1467.9	22.1
40°-50°	439.4	6.6
50°-60°	77.5	1.2
60°-70°	22.0	0.3
70°-80°	10.8	0.2
80°-90°	3.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4635.8	69.6
0°-40°	6103.7	91.7
0°-60°	6620.6	99.5
0°-90°	6656.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6656.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6554	
5°	6535	631
15°	6570	1820
25°	4836	2184
35°	2364	1468
45°	489	439
55°	80	78
65°	19	22
75°	9	11
85°	3	3
90°	0	



TEST NUMBER: P794569

CATALOG NUMBER: LER6D60D010-EC6DR6555659035-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	6554.2
2.5°	6582.1
5°	6534.6
7.5°	6633.4
10°	6687.4
12.5°	6674.3
15°	6570.0
17.5°	6314.8
20°	5884.5
22.5°	5377.8
25°	4835.8
27.5°	4223.9
30°	3537.4
32.5°	2915.3
35°	2363.9
37.5°	1819.0
40°	1304.9
42.5°	852.2
45°	489.0
47.5°	258.9
50°	161.1
52.5°	111.8
55°	80.1
57.5°	57.7
60°	40.0
62.5°	26.1
65°	18.6
67.5°	16.8
70°	15.8
72.5°	12.1
75°	9.3
77.5°	8.4
80°	6.5
82.5°	4.7
85°	2.8
87.5°	1.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)