

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793081

Luminaire Tested: LER6D45BD010-EC6DR6040509035-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P793081
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D45BD010-EC6DR6040509035-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5217.9 lumens
Efficiency: N/A
Efficacy: 134.8 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P793081

CATALOG NUMBER: LER6D45BD010-EC6DR6040509035-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P793081

CATALOG NUMBER: LER6D45BD010-EC6DR6040509035-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93															
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86				86															
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80				80															
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75				75															
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70				70															
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66				66															
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62				62															
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59				59															
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55				55															
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53				53															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	677078
5°	693736
10°	702112
15°	668849
20°	589724
25°	476979
30°	322638
35°	161673
40°	26230
45°	25665
50°	26177
55°	26573
60°	27315
65°	27947
70°	28591
75°	28960
80°	27937
85°	23192

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 28960 cd/sqm



TEST NUMBER: P793081

CATALOG NUMBER: LER6D45BD010-EC6DR6040509035-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	604.5	11.6
10°-20°	1635.6	31.3
20°-30°	1759.8	33.7
30°-40°	764.9	14.7
40°-50°	128.5	2.5
50°-60°	124.9	2.4
60°-70°	106.8	2.0
70°-80°	71.5	1.4
80°-90°	21.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3999.9	76.7
0°-40°	4764.8	91.3
0°-60°	5018.2	96.2
0°-90°	5217.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5217.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6197	
5°	6325	605
15°	5913	1636
25°	3956	1760
35°	1212	765
45°	166	128
55°	140	125
65°	108	107
75°	69	72
85°	18	21
90°	0	



TEST NUMBER: P793081

CATALOG NUMBER: LER6D45BD010-EC6DR6040509035-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	6196.9
2.5°	6371.1
5°	6325.2
7.5°	6339.7
10°	6328.4
12.5°	6197.7
15°	5913.0
17.5°	5530.8
20°	5071.9
22.5°	4580.8
25°	3956.5
27.5°	3164.6
30°	2557.3
32.5°	1971.0
35°	1212.1
37.5°	518.6
40°	183.9
42.5°	169.4
45°	166.1
47.5°	160.5
50°	154.0
52.5°	146.8
55°	139.5
57.5°	132.3
60°	125.0
62.5°	116.9
65°	108.1
67.5°	99.2
70°	89.5
72.5°	79.0
75°	68.6
77.5°	56.5
80°	44.4
82.5°	31.5
85°	18.5
87.5°	6.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)