

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794571

Luminaire Tested: LER6D60D010-EC6DR6555659035-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P794571
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D60D010-EC6DR6555659035-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6196.2 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P794571

CATALOG NUMBER: LER6D60D010-EC6DR6555659035-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P794571

CATALOG NUMBER: LER6D60D010-EC6DR6555659035-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	328580
5°	327748
10°	327469
15°	317376
20°	288933
25°	251786
30°	209412
35°	165932
40°	119759
45°	75658
50°	39433
55°	20966
60°	11003
65°	6053
70°	2544
75°	2798
80°	1951
85°	1675

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 75658 cd/sqm



TEST NUMBER: P794571

CATALOG NUMBER: LER6D60D010-EC6DR6555659035-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	532.0	8.6
10°-20°	1456.9	23.5
20°-30°	1780.9	28.7
30°-40°	1444.9	23.3
40°-50°	720.0	11.6
50°-60°	200.8	3.2
60°-70°	45.6	0.7
70°-80°	11.9	0.2
80°-90°	3.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3769.8	60.8
0°-40°	5214.8	84.2
0°-60°	6135.6	99.0
0°-90°	6196.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6196.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5626	
5°	5590	532
15°	5249	1457
25°	3907	1781
35°	2327	1445
45°	916	720
55°	206	201
65°	44	46
75°	12	12
85°	2	3
90°	0	



TEST NUMBER: P794571

CATALOG NUMBER: LER6D60D010-EC6DR6555659035-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	5626.0
2.5°	5621.8
5°	5590.4
7.5°	5572.2
10°	5521.8
12.5°	5419.3
15°	5249.0
17.5°	4982.8
20°	4648.8
22.5°	4288.3
25°	3907.2
27.5°	3499.6
30°	3105.2
32.5°	2715.8
35°	2327.3
37.5°	1939.5
40°	1570.8
42.5°	1225.2
45°	916.0
47.5°	638.2
50°	434.0
52.5°	299.3
55°	205.9
57.5°	138.9
60°	94.2
62.5°	65.3
65°	43.8
67.5°	22.3
70°	14.9
72.5°	14.1
75°	12.4
77.5°	8.3
80°	5.8
82.5°	4.1
85°	2.5
87.5°	1.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)