

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793113

Luminaire Tested: LER6D45BD010-EC6DR6540509027-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P793113
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D45BD010-EC6DR6540509027-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4379.4 lumens
Efficiency: N/A
Efficacy: 113.2 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P793113

CATALOG NUMBER: LER6D45BD010-EC6DR6540509027-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P793113

CATALOG NUMBER: LER6D45BD010-EC6DR6540509027-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	471111
5°	471495
10°	488097
15°	488906
20°	450127
25°	383524
30°	293608
35°	207424
40°	122433
45°	49708
50°	18018
55°	10039
60°	5747
65°	3180
70°	3322
75°	2575
80°	2706
85°	2257

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 49708 cd/sqm



TEST NUMBER: P793113

CATALOG NUMBER: LER6D45BD010-EC6DR6540509027-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	415.2	9.5
10°-20°	1197.6	27.3
20°-30°	1436.9	32.8
30°-40°	965.7	22.1
40°-50°	289.1	6.6
50°-60°	51.0	1.2
60°-70°	14.5	0.3
70°-80°	7.1	0.2
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3049.8	69.6
0°-40°	4015.4	91.7
0°-60°	4355.5	99.5
0°-90°	4379.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4379.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4312	
5°	4299	415
15°	4322	1198
25°	3181	1437
35°	1555	966
45°	322	289
55°	53	51
65°	12	15
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P793113

CATALOG NUMBER: LER6D45BD010-EC6DR6540509027-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4311.8
2.5°	4330.2
5°	4298.9
7.5°	4363.9
10°	4399.4
12.5°	4390.9
15°	4322.2
17.5°	4154.3
20°	3871.3
22.5°	3537.9
25°	3181.3
27.5°	2778.8
30°	2327.2
32.5°	1917.9
35°	1555.1
37.5°	1196.7
40°	858.4
42.5°	560.7
45°	321.7
47.5°	170.3
50°	106.0
52.5°	73.5
55°	52.7
57.5°	38.0
60°	26.3
62.5°	17.2
65°	12.3
67.5°	11.0
70°	10.4
72.5°	8.0
75°	6.1
77.5°	5.5
80°	4.3
82.5°	3.1
85°	1.8
87.5°	1.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)