

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794587

Luminaire Tested: LER6D60D010-EC6DR6555659050-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P794587
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D60D010-EC6DR6555659050-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6532.2 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P794587

CATALOG NUMBER: LER6D60D010-EC6DR6555659050-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P794587

CATALOG NUMBER: LER6D60D010-EC6DR6555659050-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	346399
5°	345524
10°	345225
15°	334584
20°	304601
25°	265441
30°	220768
35°	174930
40°	126255
45°	79763
50°	41578
55°	22096
60°	11611
65°	6385
70°	2681
75°	2956
80°	2052
85°	1742

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 79763 cd/sqm



TEST NUMBER: P794587

CATALOG NUMBER: LER6D60D010-EC6DR6555659050-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	560.9	8.6
10°-20°	1535.9	23.5
20°-30°	1877.4	28.7
30°-40°	1523.3	23.3
40°-50°	759.1	11.6
50°-60°	211.7	3.2
60°-70°	48.1	0.7
70°-80°	12.5	0.2
80°-90°	3.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3974.3	60.8
0°-40°	5497.6	84.2
0°-60°	6468.4	99.0
0°-90°	6532.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6532.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5931	
5°	5894	561
15°	5534	1536
25°	4119	1877
35°	2454	1523
45°	966	759
55°	217	212
65°	46	48
75°	13	13
85°	3	3
90°	0	



TEST NUMBER: P794587

CATALOG NUMBER: LER6D60D010-EC6DR6555659050-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	5931.1
2.5°	5926.7
5°	5893.6
7.5°	5874.4
10°	5821.2
12.5°	5713.2
15°	5533.6
17.5°	5253.0
20°	4900.9
22.5°	4520.8
25°	4119.1
27.5°	3689.4
30°	3273.6
32.5°	2863.1
35°	2453.5
37.5°	2044.7
40°	1656.0
42.5°	1291.7
45°	965.7
47.5°	672.9
50°	457.6
52.5°	315.5
55°	217.0
57.5°	146.4
60°	99.4
62.5°	68.9
65°	46.2
67.5°	23.5
70°	15.7
72.5°	14.8
75°	13.1
77.5°	8.7
80°	6.1
82.5°	4.4
85°	2.6
87.5°	1.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)