

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794590

Luminaire Tested: LER6D60D010-EC6DR6555659050-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P794590
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D60D010-EC6DR6555659050-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6685.3 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P794590

CATALOG NUMBER: LER6D60D010-EC6DR6555659050-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P794590

CATALOG NUMBER: LER6D60D010-EC6DR6555659050-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	354517
5°	353620
10°	353320
15°	342427
20°	311736
25°	271660
30°	225948
35°	179029
40°	129213
45°	81629
50°	42550
55°	22615
60°	11879
65°	6537
70°	2749
75°	3024
80°	2085
85°	1809

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 81629 cd/sqm



TEST NUMBER: P794590

CATALOG NUMBER: LER6D60D010-EC6DR6555659050-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	574.0	8.6
10°-20°	1571.9	23.5
20°-30°	1921.4	28.7
30°-40°	1559.0	23.3
40°-50°	776.9	11.6
50°-60°	216.7	3.2
60°-70°	49.3	0.7
70°-80°	12.8	0.2
80°-90°	3.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4067.4	60.8
0°-40°	5626.4	84.2
0°-60°	6619.9	99.0
0°-90°	6685.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6685.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6070	
5°	6032	574
15°	5663	1572
25°	4216	1921
35°	2511	1559
45°	988	777
55°	222	217
65°	47	49
75°	13	13
85°	3	3
90°	0	



TEST NUMBER: P794590

CATALOG NUMBER: LER6D60D010-EC6DR6555659050-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	6070.1
2.5°	6065.6
5°	6031.7
7.5°	6012.1
10°	5957.7
12.5°	5847.1
15°	5663.3
17.5°	5376.1
20°	5015.7
22.5°	4626.8
25°	4215.6
27.5°	3775.8
30°	3350.4
32.5°	2930.2
35°	2511.0
37.5°	2092.6
40°	1694.8
42.5°	1321.9
45°	988.3
47.5°	688.6
50°	468.3
52.5°	322.9
55°	222.1
57.5°	149.9
60°	101.7
62.5°	70.5
65°	47.3
67.5°	24.1
70°	16.1
72.5°	15.2
75°	13.4
77.5°	8.9
80°	6.2
82.5°	4.5
85°	2.7
87.5°	1.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)