

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794602

Luminaire Tested: LER6D60D010-EC6DR7055659027-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P794602
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D60D010-EC6DR7055659027-6LB DP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5479.6 lumens
Efficiency: N/A
Efficacy: 85.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P794602
CATALOG NUMBER: LER6D60D010-EC6DR7055659027-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P794602

CATALOG NUMBER: LER6D60D010-EC6DR7055659027-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	673112
5°	653111
10°	634912
15°	626578
20°	585097
25°	439547
30°	310728
35°	110067
40°	57879
45°	61637
50°	63827
55°	65033
60°	65425
65°	64064
70°	60441
75°	56019
80°	49707
85°	40367

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 65459 cd/sqm



TEST NUMBER: P794602

CATALOG NUMBER: LER6D60D010-EC6DR7055659027-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	561.7	10.3
10°-20°	1540.6	28.1
20°-30°	1696.8	31.0
30°-40°	648.3	11.8
40°-50°	306.1	5.6
50°-60°	304.3	5.6
60°-70°	243.7	4.4
70°-80°	140.1	2.6
80°-90°	38.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3799.1	69.3
0°-40°	4447.4	81.2
0°-60°	5057.8	92.3
0°-90°	5479.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5479.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6161	
5°	5955	562
15°	5539	1541
25°	3646	1697
35°	825	648
45°	399	306
55°	341	304
65°	248	244
75°	133	140
85°	32	38
90°	0	



TEST NUMBER: P794602

CATALOG NUMBER: LER6D60D010-EC6DR7055659027-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	6160.6
2.5°	6096.2
5°	5954.8
7.5°	5836.8
10°	5722.7
12.5°	5626.1
15°	5539.3
17.5°	5329.6
20°	5032.1
22.5°	4390.3
25°	3646.0
27.5°	3174.0
30°	2462.9
32.5°	1590.9
35°	825.2
37.5°	445.8
40°	405.8
42.5°	402.8
45°	398.9
47.5°	390.2
50°	375.5
52.5°	358.9
55°	341.4
57.5°	321.9
60°	299.4
62.5°	274.1
65°	247.8
67.5°	218.5
70°	189.2
72.5°	160.0
75°	132.7
77.5°	104.4
80°	79.0
82.5°	55.6
85°	32.2
87.5°	12.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)