

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793127

Luminaire Tested: LER6D45BD010-EC6DR6540509035-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P793127
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D45BD010-EC6DR6540509035-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3234.5 lumens
Efficiency: N/A
Efficacy: 83.6 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P793127

CATALOG NUMBER: LER6D45BD010-EC6DR6540509035-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P793127

CATALOG NUMBER: LER6D45BD010-EC6DR6540509035-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93					93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87					87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80					80			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75					75			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69					69			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65					65			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60					60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57					57			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53					53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50					50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	347941
5°	348228
10°	360487
15°	361086
20°	332436
25°	283258
30°	216837
35°	153190
40°	90427
45°	36713
50°	13309
55°	7410
60°	4261
65°	2353
70°	2460
75°	1900
80°	2013
85°	1755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 36713 cd/sqm



TEST NUMBER: P793127

CATALOG NUMBER: LER6D45BD010-EC6DR6540509035-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	306.6	9.5
10°-20°	884.5	27.3
20°-30°	1061.3	32.8
30°-40°	713.2	22.0
40°-50°	213.5	6.6
50°-60°	37.7	1.2
60°-70°	10.7	0.3
70°-80°	5.3	0.2
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2252.4	69.6
0°-40°	2965.6	91.7
0°-60°	3216.8	99.5
0°-90°	3234.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3234.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3184	
5°	3175	307
15°	3192	885
25°	2350	1061
35°	1148	713
45°	238	214
55°	39	38
65°	9	11
75°	4	5
85°	1	2
90°	0	



TEST NUMBER: P793127

CATALOG NUMBER: LER6D45BD010-EC6DR6540509035-6LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	3184.5
2.5°	3198.1
5°	3175.0
7.5°	3223.0
10°	3249.2
12.5°	3242.9
15°	3192.2
17.5°	3068.2
20°	2859.1
22.5°	2613.0
25°	2349.6
27.5°	2052.3
30°	1718.7
32.5°	1416.4
35°	1148.5
37.5°	883.8
40°	634.0
42.5°	414.1
45°	237.6
47.5°	125.8
50°	78.3
52.5°	54.3
55°	38.9
57.5°	28.1
60°	19.5
62.5°	12.7
65°	9.1
67.5°	8.1
70°	7.7
72.5°	5.9
75°	4.5
77.5°	4.1
80°	3.2
82.5°	2.3
85°	1.4
87.5°	0.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)