

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794624

Luminaire Tested: LER6D60D010-EC6DR7055659040-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P794624
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D60D010-EC6DR7055659040-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7644.9 lumens
Efficiency: N/A
Efficacy: 118.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P794624
CATALOG NUMBER: LER6D60D010-EC6DR7055659040-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P794624

CATALOG NUMBER: LER6D60D010-EC6DR7055659040-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	939096
5°	911195
10°	885795
15°	874176
20°	816294
25°	613244
30°	433510
35°	153564
40°	80743
45°	86005
50°	89052
55°	90731
60°	91298
65°	89375
70°	84337
75°	78140
80°	69339
85°	56288

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 91325 cd/sqm



TEST NUMBER: P794624

CATALOG NUMBER: LER6D60D010-EC6DR7055659040-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	783.6	10.3
10°-20°	2149.4	28.1
20°-30°	2367.3	31.0
30°-40°	904.5	11.8
40°-50°	427.1	5.6
50°-60°	424.6	5.6
60°-70°	339.9	4.4
70°-80°	195.4	2.6
80°-90°	53.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5300.3	69.3
0°-40°	6204.8	81.2
0°-60°	7056.4	92.3
0°-90°	7644.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7644.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8595	
5°	8308	784
15°	7728	2149
25°	5087	2367
35°	1151	904
45°	557	427
55°	476	425
65°	346	340
75°	185	195
85°	45	53
90°	0	



TEST NUMBER: P794624

CATALOG NUMBER: LER6D60D010-EC6DR7055659040-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	8595.0
2.5°	8505.2
5°	8307.9
7.5°	8143.2
10°	7984.0
12.5°	7849.3
15°	7728.2
17.5°	7435.6
20°	7020.5
22.5°	6125.1
25°	5086.8
27.5°	4428.1
30°	3436.1
32.5°	2219.5
35°	1151.3
37.5°	621.9
40°	566.1
42.5°	562.0
45°	556.6
47.5°	544.3
50°	523.9
52.5°	500.8
55°	476.3
57.5°	449.1
60°	417.8
62.5°	382.4
65°	345.7
67.5°	304.8
70°	264.0
72.5°	223.2
75°	185.1
77.5°	145.6
80°	110.2
82.5°	77.6
85°	44.9
87.5°	17.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)