

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793466

Luminaire Tested: LER6D50D010-EC6DR5040509035-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P793466
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D50D010-EC6DR5040509035-6LB DP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5741.9 lumens
Efficiency: N/A
Efficacy: 122.2 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P793466

CATALOG NUMBER: LER6D50D010-EC6DR5040509035-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P793466

CATALOG NUMBER: LER6D50D010-EC6DR5040509035-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95					95			
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90					90			
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85					85			
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80					80			
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76					76			
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72					72			
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69					69			
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65					65			
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62					62			
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59					59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1010848
5°	1000242
10°	983772
15°	895803
20°	745414
25°	529132
30°	280070
35°	114136
40°	42390
45°	19407
50°	7955
55°	4153
60°	2054
65°	595
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19407 cd/sqm



TEST NUMBER: P793466

CATALOG NUMBER: LER6D50D010-EC6DR5040509035-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	862.0	15.0
10°-20°	2178.5	37.9
20°-30°	1956.9	34.1
30°-40°	612.7	10.7
40°-50°	107.3	1.9
50°-60°	21.4	0.4
60°-70°	3.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4997.3	87.0
0°-40°	5610.0	97.7
0°-60°	5738.7	99.9
0°-90°	5741.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5741.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9252	
5°	9120	862
15°	7919	2178
25°	4389	1957
35°	856	613
45°	126	107
55°	22	21
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P793466

CATALOG NUMBER: LER6D50D010-EC6DR5040509035-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	9251.7
2.5°	9205.6
5°	9119.8
7.5°	8988.8
10°	8867.1
12.5°	8477.1
15°	7919.4
17.5°	7211.2
20°	6410.9
22.5°	5485.0
25°	4389.1
27.5°	3226.9
30°	2219.9
32.5°	1445.4
35°	855.7
37.5°	491.4
40°	297.2
42.5°	193.4
45°	125.6
47.5°	76.4
50°	46.8
52.5°	32.0
55°	21.8
57.5°	14.8
60°	9.4
62.5°	5.5
65°	2.3
67.5°	0.8
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)