

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794922

Luminaire Tested: LER6D65D010-EC6DR5055659050-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P794922
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D65D010-EC6DR5055659050-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8323.4 lumens
Efficiency: N/A
Efficacy: 114.3 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P794922

CATALOG NUMBER: LER6D65D010-EC6DR5055659050-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P794922
 CATALOG NUMBER: LER6D65D010-EC6DR5055659050-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95																												
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90																												
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85																												
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80																												
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76																												
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72																												
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69																												
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65																												
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62																												
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1465307
5°	1449945
10°	1426059
15°	1298550
20°	1080535
25°	767025
30°	405981
35°	165448
40°	61445
45°	28122
50°	11525
55°	6039
60°	2972
65°	879
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 28122 cd/sqm



TEST NUMBER: P794922

CATALOG NUMBER: LER6D65D010-EC6DR5055659050-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1249.5	15.0
10°-20°	3157.9	37.9
20°-30°	2836.6	34.1
30°-40°	888.1	10.7
40°-50°	155.5	1.9
50°-60°	31.0	0.4
60°-70°	4.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7244.1	87.0
0°-40°	8132.2	97.7
0°-60°	8318.7	99.9
0°-90°	8323.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8323.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13411	
5°	13220	###
15°	11480	3158
25°	6362	2837
35°	1240	888
45°	182	155
55°	32	31
65°	3	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P794922

CATALOG NUMBER: LER6D65D010-EC6DR5055659050-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	13411.1
2.5°	13344.4
5°	13220.0
7.5°	13030.0
10°	12853.6
12.5°	12288.3
15°	11479.9
17.5°	10453.2
20°	9293.1
22.5°	7951.0
25°	6362.4
27.5°	4677.6
30°	3217.9
32.5°	2095.2
35°	1240.4
37.5°	712.3
40°	430.8
42.5°	280.4
45°	182.0
47.5°	110.8
50°	67.8
52.5°	46.4
55°	31.7
57.5°	21.5
60°	13.6
62.5°	7.9
65°	3.4
67.5°	1.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)