

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793598

Luminaire Tested: LER6D50D010-EC6DR6540509027-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P793598
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D50D010-EC6DR6540509027-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4899.4 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P793598

CATALOG NUMBER: LER6D50D010-EC6DR6540509027-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P793598

CATALOG NUMBER: LER6D50D010-EC6DR6540509027-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	259810
5°	259155
10°	258937
15°	250956
20°	228465
25°	199092
30°	165590
35°	131203
40°	94699
45°	59824
50°	31183
55°	16577
60°	8702
65°	4782
70°	2015
75°	2211
80°	1547
85°	1340

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 59824 cd/sqm



TEST NUMBER: P793598

CATALOG NUMBER: LER6D50D010-EC6DR6540509027-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	420.7	8.6
10°-20°	1152.0	23.5
20°-30°	1408.2	28.7
30°-40°	1142.5	23.3
40°-50°	569.4	11.6
50°-60°	158.8	3.2
60°-70°	36.1	0.7
70°-80°	9.4	0.2
80°-90°	2.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2980.9	60.8
0°-40°	4123.4	84.2
0°-60°	4851.6	99.0
0°-90°	4899.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4899.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4448	
5°	4420	421
15°	4150	1152
25°	3090	1408
35°	1840	1143
45°	724	569
55°	163	159
65°	35	36
75°	10	9
85°	2	2
90°	0	



TEST NUMBER: P793598

CATALOG NUMBER: LER6D50D010-EC6DR6540509027-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4448.5
2.5°	4445.3
5°	4420.4
7.5°	4406.1
10°	4366.2
12.5°	4285.1
15°	4150.5
17.5°	3940.0
20°	3675.9
22.5°	3390.8
25°	3089.5
27.5°	2767.2
30°	2455.4
32.5°	2147.5
35°	1840.2
37.5°	1533.6
40°	1242.1
42.5°	968.8
45°	724.3
47.5°	504.7
50°	343.2
52.5°	236.6
55°	162.8
57.5°	109.8
60°	74.5
62.5°	51.6
65°	34.6
67.5°	17.7
70°	11.8
72.5°	11.1
75°	9.8
77.5°	6.5
80°	4.6
82.5°	3.3
85°	2.0
87.5°	1.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)