

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P795008

Luminaire Tested: LER6D65D010-EC6DR6055659040-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P795008
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D65D010-EC6DR6055659040-6LB DP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8400.0 lumens
Efficiency: N/A
Efficacy: 115.4 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P795008
CATALOG NUMBER: LER6D65D010-EC6DR6055659040-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P795008

CATALOG NUMBER: LER6D65D010-EC6DR6055659040-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1089985
5°	1116797
10°	1130287
15°	1076742
20°	949356
25°	767869
30°	519402
35°	260270
40°	42218
45°	41318
50°	42155
55°	42784
60°	43967
65°	44985
70°	46034
75°	46605
80°	44925
85°	37483

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 46605 cd/sqm



TEST NUMBER: P795008

CATALOG NUMBER: LER6D65D010-EC6DR6055659040-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	973.2	11.6
10°-20°	2633.0	31.3
20°-30°	2832.9	33.7
30°-40°	1231.4	14.7
40°-50°	206.8	2.5
50°-60°	201.1	2.4
60°-70°	172.0	2.0
70°-80°	115.1	1.4
80°-90°	34.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6439.1	76.7
0°-40°	7670.5	91.3
0°-60°	8078.4	96.2
0°-90°	8400.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8400.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9976	
5°	10182	973
15°	9519	2633
25°	6369	2833
35°	1951	1231
45°	267	207
55°	225	201
65°	174	172
75°	110	115
85°	30	34
90°	0	



TEST NUMBER: P795008

CATALOG NUMBER: LER6D65D010-EC6DR6055659040-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	9976.0
2.5°	10256.5
5°	10182.5
7.5°	10205.8
10°	10187.7
12.5°	9977.3
15°	9519.0
17.5°	8903.7
20°	8164.9
22.5°	7374.3
25°	6369.4
27.5°	5094.5
30°	4116.9
32.5°	3173.0
35°	1951.3
37.5°	834.8
40°	296.0
42.5°	272.6
45°	267.4
47.5°	258.4
50°	248.0
52.5°	236.3
55°	224.6
57.5°	212.9
60°	201.2
62.5°	188.3
65°	174.0
67.5°	159.7
70°	144.1
72.5°	127.2
75°	110.4
77.5°	90.9
80°	71.4
82.5°	50.6
85°	29.9
87.5°	10.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)