

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793648

Luminaire Tested: LER6D50D010-EC6DR7040509030-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P793648
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D50D010-EC6DR7040509030-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5813.2 lumens
Efficiency: N/A
Efficacy: 123.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P793648

CATALOG NUMBER: LER6D50D010-EC6DR7040509030-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P793648

CATALOG NUMBER: LER6D50D010-EC6DR7040509030-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	714096
5°	692881
10°	673566
15°	664721
20°	620711
25°	466310
30°	329640
35°	116763
40°	61402
45°	65392
50°	67720
55°	68996
60°	69424
65°	67942
70°	64115
75°	59397
80°	52728
85°	42749

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 69445 cd/sqm



TEST NUMBER: P793648

CATALOG NUMBER: LER6D50D010-EC6DR7040509030-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	595.9	10.3
10°-20°	1634.4	28.1
20°-30°	1800.1	31.0
30°-40°	687.8	11.8
40°-50°	324.7	5.6
50°-60°	322.9	5.6
60°-70°	258.5	4.4
70°-80°	148.5	2.6
80°-90°	40.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4030.4	69.3
0°-40°	4718.1	81.2
0°-60°	5365.7	92.3
0°-90°	5813.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5813.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6536	
5°	6317	596
15°	5876	1634
25°	3868	1800
35°	875	688
45°	423	325
55°	362	323
65°	263	258
75°	141	149
85°	34	40
90°	0	



TEST NUMBER: P793648

CATALOG NUMBER: LER6D50D010-EC6DR7040509030-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	6535.7
2.5°	6467.4
5°	6317.4
7.5°	6192.1
10°	6071.1
12.5°	5968.6
15°	5876.5
17.5°	5654.1
20°	5338.4
22.5°	4657.6
25°	3868.0
27.5°	3367.2
30°	2612.8
32.5°	1687.7
35°	875.4
37.5°	472.9
40°	430.5
42.5°	427.4
45°	423.2
47.5°	413.9
50°	398.4
52.5°	380.8
55°	362.2
57.5°	341.5
60°	317.7
62.5°	290.8
65°	262.8
67.5°	231.8
70°	200.7
72.5°	169.7
75°	140.7
77.5°	110.7
80°	83.8
82.5°	59.0
85°	34.1
87.5°	13.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)