

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793657

Luminaire Tested: LER6D50D010-EC6DR7040509035-6LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P793657  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D50D010-EC6DR7040509035-6LBDDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6168.2 lumens  
Efficiency: N/A  
Efficacy: 131.2 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 47  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P793657  
CATALOG NUMBER: LER6D50D010-EC6DR7040509035-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P793657  
 CATALOG NUMBER: LER6D50D010-EC6DR7040509035-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	757701
5°	735183
10°	714694
15°	705318
20°	658616
25°	494786
30°	349776
35°	123899
40°	65153
45°	69394
50°	71850
55°	73205
60°	73664
65°	72105
70°	68044
75°	63027
80°	55937
85°	45381

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 73674 cd/sqm



TEST NUMBER: P793657

CATALOG NUMBER: LER6D50D010-EC6DR7040509035-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	632.2	10.3
10°-20°	1734.2	28.1
20°-30°	1910.0	31.0
30°-40°	729.8	11.8
40°-50°	344.6	5.6
50°-60°	342.6	5.6
60°-70°	274.3	4.4
70°-80°	157.6	2.6
80°-90°	42.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4276.5	69.3
0°-40°	5006.3	81.2
0°-60°	5693.4	92.3
0°-90°	6168.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6168.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6935	
5°	6703	632
15°	6235	1734
25°	4104	1910
35°	929	730
45°	449	345
55°	384	343
65°	279	274
75°	149	158
85°	36	43
90°	0	



TEST NUMBER: P793657

CATALOG NUMBER: LER6D50D010-EC6DR7040509035-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6934.8
2.5°	6862.3
5°	6703.1
7.5°	6570.2
10°	6441.8
12.5°	6333.1
15°	6235.4
17.5°	5999.3
20°	5664.4
22.5°	4942.0
25°	4104.2
27.5°	3572.8
30°	2772.4
32.5°	1790.8
35°	928.9
37.5°	501.8
40°	456.8
42.5°	453.5
45°	449.1
47.5°	439.2
50°	422.7
52.5°	404.1
55°	384.3
57.5°	362.3
60°	337.1
62.5°	308.5
65°	278.9
67.5°	245.9
70°	213.0
72.5°	180.1
75°	149.3
77.5°	117.5
80°	88.9
82.5°	62.6
85°	36.2
87.5°	14.3
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)