

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P795050

Luminaire Tested: LER6D65D010-EC6DR6555659035-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P795050
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D65D010-EC6DR6555659035-6LBDDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6049.7 lumens
Efficiency: N/A
Efficacy: 83.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P795050
CATALOG NUMBER: LER6D65D010-EC6DR6555659035-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P795050

CATALOG NUMBER: LER6D65D010-EC6DR6555659035-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	650801
5°	651334
10°	674265
15°	675387
20°	621804
25°	529807
30°	405590
35°	286546
40°	169145
45°	68668
50°	24885
55°	13868
60°	7954
65°	4369
70°	4600
75°	3588
80°	3712
85°	3134

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 68668 cd/sqm



TEST NUMBER: P795050

CATALOG NUMBER: LER6D65D010-EC6DR6555659035-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	573.5	9.5
10°-20°	1654.4	27.3
20°-30°	1985.0	32.8
30°-40°	1334.0	22.1
40°-50°	399.3	6.6
50°-60°	70.5	1.2
60°-70°	20.0	0.3
70°-80°	9.8	0.2
80°-90°	3.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4213.0	69.6
0°-40°	5547.0	91.7
0°-60°	6016.8	99.5
0°-90°	6049.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6049.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5956	
5°	5939	574
15°	5971	1654
25°	4395	1985
35°	2148	1334
45°	444	399
55°	73	70
65°	17	20
75°	8	10
85°	2	3
90°	0	



TEST NUMBER: P795050

CATALOG NUMBER: LER6D65D010-EC6DR6555659035-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5956.4
2.5°	5981.8
5°	5938.6
7.5°	6028.4
10°	6077.4
12.5°	6065.6
15°	5970.8
17.5°	5738.9
20°	5347.8
22.5°	4887.4
25°	4394.7
27.5°	3838.6
30°	3214.8
32.5°	2649.4
35°	2148.3
37.5°	1653.1
40°	1185.9
42.5°	774.5
45°	444.4
47.5°	235.3
50°	146.4
52.5°	101.6
55°	72.8
57.5°	52.5
60°	36.4
62.5°	23.7
65°	16.9
67.5°	15.2
70°	14.4
72.5°	11.0
75°	8.5
77.5°	7.6
80°	5.9
82.5°	4.2
85°	2.5
87.5°	1.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)