

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P795051

Luminaire Tested: LER6D65D010-EC6DR6555659035-6LBS1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P795051  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D65D010-EC6DR6555659035-6LBS1B  
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6852.8 lumens  
Efficiency: N/A  
Efficacy: 94.1 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 72.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P795051

CATALOG NUMBER: LER6D65D010-EC6DR6555659035-6LBS1B

### Luminous Intensity Polar Plot





TEST NUMBER: P795051

CATALOG NUMBER: LER6D65D010-EC6DR6555659035-6LBS1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93						93													
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85						85													
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78						78													
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72						72													
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66						66													
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61						61													
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56						56													
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52						52													
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49						49													
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46						46													

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	363401
5°	362485
10°	362175
15°	351012
20°	319549
25°	278471
30°	231606
35°	183514
40°	132453
45°	83678
50°	43613
55°	23185
60°	12171
65°	6702
70°	2818
75°	3091
80°	2153
85°	1809

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 83678 cd/sqm



TEST NUMBER: P795051

CATALOG NUMBER: LER6D65D010-EC6DR6555659035-6LBS1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	588.4	8.6
10°-20°	1611.3	23.5
20°-30°	1969.6	28.7
30°-40°	1598.1	23.3
40°-50°	796.4	11.6
50°-60°	222.1	3.2
60°-70°	50.5	0.7
70°-80°	13.1	0.2
80°-90°	3.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4169.3	60.8
0°-40°	5767.4	84.2
0°-60°	6785.9	99.0
0°-90°	6852.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6852.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6222	
5°	6183	588
15°	5805	1611
25°	4321	1970
35°	2574	1598
45°	1013	796
55°	228	222
65°	48	50
75°	14	13
85°	3	3
90°	0	



TEST NUMBER: P795051

CATALOG NUMBER: LER6D65D010-EC6DR6555659035-6LBS1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6222.2
2.5°	6217.6
5°	6182.9
7.5°	6162.8
10°	6107.0
12.5°	5993.6
15°	5805.3
17.5°	5510.8
20°	5141.4
22.5°	4742.8
25°	4321.3
27.5°	3870.5
30°	3434.3
32.5°	3003.7
35°	2573.9
37.5°	2145.1
40°	1737.3
42.5°	1355.1
45°	1013.1
47.5°	705.9
50°	480.0
52.5°	331.0
55°	227.7
57.5°	153.6
60°	104.2
62.5°	72.2
65°	48.5
67.5°	24.7
70°	16.5
72.5°	15.5
75°	13.7
77.5°	9.1
80°	6.4
82.5°	4.6
85°	2.7
87.5°	1.8
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)