

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P795052

Luminaire Tested: LER6D65D010-EC6DR6555659035-6LBS1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P795052  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D65D010-EC6DR6555659035-6LBS1H  
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7380.9 lumens  
Efficiency: N/A  
Efficacy: 101.4 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct

Input Watts (W): 72.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P795052

CATALOG NUMBER: LER6D65D010-EC6DR6555659035-6LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P795052

CATALOG NUMBER: LER6D65D010-EC6DR6555659035-6LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	391399
5°	390415
10°	390078
15°	378058
20°	344173
25°	299924
30°	249450
35°	197652
40°	142654
45°	90128
50°	46975
55°	24967
60°	13118
65°	7214
70°	3022
75°	3340
80°	2321
85°	2010

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 90128 cd/sqm



TEST NUMBER: P795052

CATALOG NUMBER: LER6D65D010-EC6DR6555659035-6LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	633.8	8.6
10°-20°	1735.5	23.5
20°-30°	2121.3	28.7
30°-40°	1721.2	23.3
40°-50°	857.7	11.6
50°-60°	239.2	3.2
60°-70°	54.4	0.7
70°-80°	14.1	0.2
80°-90°	3.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4490.6	60.8
0°-40°	6211.8	84.2
0°-60°	7308.7	99.0
0°-90°	7380.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7380.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6702	
5°	6659	634
15°	6253	1735
25°	4654	2121
35°	2772	1721
45°	1091	858
55°	245	239
65°	52	54
75°	15	14
85°	3	4
90°	0	



TEST NUMBER: P795052

CATALOG NUMBER: LER6D65D010-EC6DR6555659035-6LBS1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6701.6
2.5°	6696.7
5°	6659.3
7.5°	6637.6
10°	6577.5
12.5°	6455.4
15°	6252.6
17.5°	5935.5
20°	5537.6
22.5°	5108.2
25°	4654.2
27.5°	4168.7
30°	3698.9
32.5°	3235.1
35°	2772.2
37.5°	2310.4
40°	1871.1
42.5°	1459.5
45°	1091.2
47.5°	760.3
50°	517.0
52.5°	356.5
55°	245.2
57.5°	165.4
60°	112.3
62.5°	77.8
65°	52.2
67.5°	26.6
70°	17.7
72.5°	16.7
75°	14.8
77.5°	9.8
80°	6.9
82.5°	4.9
85°	3.0
87.5°	2.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)