

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P795068

Luminaire Tested: LER6D65D010-EC6DR6555659050-6LBS1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P795068  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D65D010-EC6DR6555659050-6LBS1H  
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7781.1 lumens  
Efficiency: N/A  
Efficacy: 106.9 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct


Input Watts (W): 72.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P795068  
CATALOG NUMBER: LER6D65D010-EC6DR6555659050-6LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P795068

CATALOG NUMBER: LER6D65D010-EC6DR6555659050-6LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	412629
5°	411585
10°	411232
15°	398555
20°	362838
25°	316189
30°	262978
35°	208375
40°	150393
45°	95010
50°	49528
55°	26322
60°	13830
65°	7601
70°	3193
75°	3520
80°	2455
85°	2077

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 95010 cd/sqm



TEST NUMBER: P795068

CATALOG NUMBER: LER6D65D010-EC6DR6555659050-6LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	668.1	8.6
10°-20°	1829.6	23.5
20°-30°	2236.4	28.7
30°-40°	1814.5	23.3
40°-50°	904.2	11.6
50°-60°	252.2	3.2
60°-70°	57.3	0.7
70°-80°	14.9	0.2
80°-90°	3.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4734.1	60.8
0°-40°	6548.7	84.2
0°-60°	7705.1	99.0
0°-90°	7781.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7781.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7065	
5°	7020	668
15°	6592	1830
25°	4907	2236
35°	2923	1815
45°	1150	904
55°	258	252
65°	55	57
75°	16	15
85°	3	4
90°	0	



TEST NUMBER: P795068

CATALOG NUMBER: LER6D65D010-EC6DR6555659050-6LBS1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7065.1
2.5°	7059.9
5°	7020.4
7.5°	6997.6
10°	6934.2
12.5°	6805.5
15°	6591.6
17.5°	6257.3
20°	5837.9
22.5°	5385.2
25°	4906.6
27.5°	4394.8
30°	3899.5
32.5°	3410.5
35°	2922.6
37.5°	2435.7
40°	1972.6
42.5°	1538.6
45°	1150.3
47.5°	801.5
50°	545.1
52.5°	375.8
55°	258.5
57.5°	174.4
60°	118.4
62.5°	82.0
65°	55.0
67.5°	28.0
70°	18.7
72.5°	17.6
75°	15.6
77.5°	10.4
80°	7.3
82.5°	5.2
85°	3.1
87.5°	2.1
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)