

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P795088

Luminaire Tested: LER6D65D010-EC6DR7055659030-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P795088
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D65D010-EC6DR7055659030-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7993.2 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P795088
CATALOG NUMBER: LER6D65D010-EC6DR7055659030-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P795088

CATALOG NUMBER: LER6D65D010-EC6DR7055659030-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	981894
5°	952719
10°	926157
15°	914004
20°	853501
25°	641189
30°	453267
35°	160553
40°	84423
45°	89914
50°	93115
55°	94864
60°	95450
65°	93434
70°	88170
75°	81686
80°	72548
85°	58920

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 95474 cd/sqm



TEST NUMBER: P795088

CATALOG NUMBER: LER6D65D010-EC6DR7055659030-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	819.3	10.3
10°-20°	2247.4	28.1
20°-30°	2475.2	31.0
30°-40°	945.7	11.8
40°-50°	446.5	5.6
50°-60°	443.9	5.6
60°-70°	355.4	4.4
70°-80°	204.3	2.6
80°-90°	55.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5541.8	69.3
0°-40°	6487.5	81.2
0°-60°	7377.9	92.3
0°-90°	7993.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7993.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8987	
5°	8686	819
15°	8080	2247
25°	5319	2475
35°	1204	946
45°	582	447
55°	498	444
65°	361	355
75°	194	204
85°	47	56
90°	0	



TEST NUMBER: P795088

CATALOG NUMBER: LER6D65D010-EC6DR7055659030-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	8986.7
2.5°	8892.8
5°	8686.5
7.5°	8514.3
10°	8347.8
12.5°	8207.0
15°	8080.3
17.5°	7774.4
20°	7340.5
22.5°	6404.2
25°	5318.6
27.5°	4629.9
30°	3592.7
32.5°	2320.7
35°	1203.7
37.5°	650.2
40°	591.9
42.5°	587.6
45°	581.9
47.5°	569.1
50°	547.8
52.5°	523.6
55°	498.0
57.5°	469.5
60°	436.8
62.5°	399.8
65°	361.4
67.5°	318.7
70°	276.0
72.5°	233.3
75°	193.5
77.5°	152.2
80°	115.3
82.5°	81.1
85°	47.0
87.5°	18.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)