

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794017

Luminaire Tested: LER6D55D010-EC6DR6055659024-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P794017
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D55D010-EC6DR6055659024-6LBDDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5874.9 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P794017

CATALOG NUMBER: LER6D55D010-EC6DR6055659024-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P794017

CATALOG NUMBER: LER6D55D010-EC6DR6055659024-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	762323
5°	781073
10°	790514
15°	753063
20°	663976
25°	537040
30°	363262
35°	182027
40°	29524
45°	28910
50°	29474
55°	29926
60°	30746
65°	31463
70°	32201
75°	32590
80°	31397
85°	26201

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 32590 cd/sqm



TEST NUMBER: P794017

CATALOG NUMBER: LER6D55D010-EC6DR6055659024-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	680.6	11.6
10°-20°	1841.5	31.3
20°-30°	1981.3	33.7
30°-40°	861.2	14.7
40°-50°	144.7	2.5
50°-60°	140.7	2.4
60°-70°	120.3	2.0
70°-80°	80.5	1.4
80°-90°	24.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4503.5	76.7
0°-40°	5364.7	91.3
0°-60°	5650.0	96.2
0°-90°	5874.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5874.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6977	
5°	7122	681
15°	6658	1842
25°	4455	1981
35°	1365	861
45°	187	145
55°	157	141
65°	122	120
75°	77	81
85°	21	24
90°	0	



TEST NUMBER: P794017

CATALOG NUMBER: LER6D55D010-EC6DR6055659024-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	6977.1
2.5°	7173.3
5°	7121.5
7.5°	7137.9
10°	7125.2
12.5°	6978.1
15°	6657.5
17.5°	6227.1
20°	5710.5
22.5°	5157.5
25°	4454.7
27.5°	3563.0
30°	2879.3
32.5°	2219.2
35°	1364.7
37.5°	583.9
40°	207.0
42.5°	190.7
45°	187.1
47.5°	180.7
50°	173.4
52.5°	165.3
55°	157.1
57.5°	148.9
60°	140.7
62.5°	131.7
65°	121.7
67.5°	111.7
70°	100.8
72.5°	89.0
75°	77.2
77.5°	63.6
80°	49.9
82.5°	35.4
85°	20.9
87.5°	7.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)